



Motor Control Products

NEMA 1 and 3/3R Enclosed AC Manual Motor Controllers/Disconnects



- Die cast aluminum enclosure, gray zinc powder coat finish
- Heavy duty flip lid, 3-sided protection
- Lockout/tagout capability



- All aluminum cover and base, base is pre-drilled for rear surface mounting
- Raintight enclosures
- Lockout/tagout capability

Enclosed AC Manual Motor Controllers/Disconnects



Enclosed Switch Motor Controllers/Disconnects					NEMA 1	NEMA 3/3R		NEMA 3R	
Ideal for use in:					Indoor Environments	Outdoor Equipment		Outdoor Environments	
Poles	HP Rating				30A	30A		30A	60A
	120V AC	240V AC	480V AC	600V AC		Thermoplastic	Aluminum Cast		
2	2	5	10	15	30102D	30322D*	30312D	30302D	—
3	3	7.5	15	20	30103D	30323D*	30313D	30303D	—
2	—	10	15	20	—	—	—	—	60302D
3	—	10	25	30	—	—	—	—	60303D
Enclosures Without Controller/Disconnect					30100	30300		30300	60300

Note: *Drill weephole to alter from NEMA 3 to NEMA 3R.

Product Dimensions Inches (mm)

	30102D, 30103D, 3100	30322D, 30323D	30302D, 30303D, 30300	60302D, 60303D, 60300
A	4.72" (120.0)	5.42" (137.7)	5.52" (140.2)	10.11" (256.8)
B	2.75" (69.8)	4.76" (120.9)	4.28" (108.7)	4.28" (108.7)
C	2.44" (61.9)	2.99" (75.9)	4.40" (111.8)	4.40" (111.8)
D	3.20" (81.2)	2.22" (56.4)	3.30" (83.3)	3.30" (83.8)
E	3.15" (80.0)	4.55" (115.6)	2.75" (69.9)	2.75" (69.9)
F	2.41" (61.3)	2.99" (75.9)	1.99" (50.5)	2.00" (50.8)
G	0.92" (23.2)	—	1.06" (26.9)	1.52" (38.6)
H	(2) " (12.7) Knockouts	—	(2) Knockouts	(2) X 1 Knockouts
I	x Knockout each end	—	—	—

