

Locking Devices



50 Amp Plugs, Connectors Flanged Devices and Receptacles

50A 250V DC 600V DC Locking Devices, 2-Pole 3-Wire and 3-Pole 4-Wire Grounding Inches (mm)



Rating	Poles/ Wires	Cord Diameter	Description	Plug	Connector	Male Flanged Devices with Lift Cover and Gasket	Receptacle Single Armored
50A 250V DC, 600V AC	2-Pole 3-Wire	.830"-1.250" (21.1-31.8)	Heavy duty Black	3763*	3762*	—	3771*
			Steel Casing	—	—	3767*	—
50A 250V DC, 600V AC	3-Pole 4-Wire	.830"-1.250" (21.1-31.8)	Heavy duty Black	3765*	3764*	—	3769*
			Steel Casing	—	—	3768*	—
50A 250V DC, 600V AC	3-Pole 4-Wire	.830"-1.250" (21.1-31.8)	Heavy duty Black	7765**	7764**	—	7379**
			Steel Casing	—	—	7968**	—

Note: *These devices are not interchangeable with other 50 amp configurations listed in this catalog.
 **These devices are intended for replacement use only in existing installations. We recommend that they not be used in new installations.
 See page H-23 for weather protective boots and accessories.

Product Dimensions Inches (mm)

	Plug	Connector	Single Receptacle	Flanged Devices
A	5.38" (162.1)	6.50" (165.1)	3.28" (83.3)	3.50" (88.9)
B	2.56" (65.0)	2.56" (65.0)	—	2.12" (53.8) SQ.
C	—	—	2.12" (53.8)	2.17" (55.1)
D	—	—	2.44" (62.0)	2.77" (70.4)
E	—	—	1.03" (26.2)	0.75" (19.1)
F	—	—	2.69" (68.3)	0.19" (4.8) Dia.

