

Locking Devices



15 and 20 Amp Locking Devices

15A 125V and 20A 250V Locking Devices Inches (mm)



| Rating | Poles/ Wires | Cord Diameter | Black/White Nylon Polarized, with Non-metallic Cord Grip | | Receptacle Black Phenolic, Back and Side Wired | | Flanged Devices Equipment Base with Binding Screw Terminals | |
|---|------------------|---------------------------|---|---------------|--|-------------|---|---------------|
| | | | Plug | Connector | Single | Duplex | Male | Female |
| NEMA L1-15, 15A 125V Plug Connector | 2-Pole 2-Wire | .296"-.562" (7.5-14.3) | 7548 | 7506 | 7535 | 7540 | 7523 | 7526 |
| NEMA L2-20, 20A 250V Plug Connector | 2-Pole 2-Wire | .296"-.562" (7.5-14.3) | 7102N 9102N* | 7101** | 7210B | — | 8808MB | 8809ER |

Note: *Plug is black/white nylon with dual non-metallic cord grip.
**Connector is thermoplastic with cord grip.

Receptacle Accessories



| Single Receptacle Wallplate | | Duplex Receptacle Wallplate | | Weatherproof Covers | | |
|-----------------------------|---------------|-----------------------------|---------------|---------------------|----------------|----------------|
| Stainless Steel | Thermoplastic | Stainless Steel | Thermoplastic | Zinc Die Cast | Zinc Die Cast | Thermoplastic |
| SS7 | P7BK | SS8 | P8BK | RW51550 | RW51470 | RW57300 |

Note: See Section Q for additional information on wallplates and weatherproof covers.

Product Dimensions Inches (mm)

| | Plug | Connector | Receptacle | | Flanged Devices |
|---|--------------|--------------|--------------------|--------------|-----------------|
| | | | Single | Duplex | Male/Female |
| A | 1.97" (50.0) | 2.78" (70.6) | 3.28" (83.3) | 3.28" (83.3) | 2.56" (65.1) |
| B | 1.53" (38.8) | 1.53" (38.8) | 2.38" (60.5) | 1.50" (38.1) | 2.19" (55.6) |
| C | | | 1.38" (34.9) | 0.91" (23.1) | 1.69" (42.9) |
| D | | | 1.00" (25.4) | 2.72" (69.1) | 1.72" (43.7) |
| E | | | 15A - 1.39" (35.3) | — | 0.06" (1.5) |
| | | | 20A - 2.09" (53.1) | — | — |

