

## 15 and 20 Amp Straight Blade Devices









### 15A and 20A Straight Blade Plugs, Connectors and Receptacles Inches (mm)

**UL Type 4, 4X, 6P**

**IP65, 66, 67, 69k\***

SUITABILITY



Rating Plug Connector	Poles/ Wires	Cord Diameter	Color	Thermoplastic Elastomer			
				Plug	Connector	Receptacle with Lift Cover	Duplex Recept. with Lift Cover
NEMA 5-15, 15A 125V  	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow Black Clear	<b>BRY14W47</b> <b>BRY14W47BK</b> <b>BRY14W47WC</b>	<b>BRY15W47</b> <b>BRY15W47BK</b> <b>BRY15W47WC</b>	<b>BRY60W47</b> <b>BRY60W47BK</b> —	<b>BRY60W47D</b> —
NEMA 6-15, 15A 250V  	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow	<b>BRY14W49</b>	<b>BRY15W49</b>	<b>BRY60W49</b>	<b>BRY60W49D</b>
NEMA 5-20, 20A 125V  	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow	<b>BRY14W33</b> <b>BRY14W33WC</b>	<b>BRY15W33</b> <b>BRY15W33WC</b>	<b>BRY60W33</b> —	<b>BRY60W33D</b> —
NEMA 6-20, 20A 250V  	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow	<b>BRY14W48</b>	<b>BRY15W48</b>	<b>BRY60W48</b>	<b>BRY60W48D</b>

Note: \*Single and duplex receptacles while in use, not with cover closed.  
Black devices are available, consult factory.

### Product Dimensions Inches (mm)

15A and 20A Straight Blade	
A	
B	
C	
D	

15A and 20A Straight Blade Receptacles	
A	4.56" (115.9)
B	3.10" (78.7)
C	1.20" (30.6)
D	3.25" (82.6)
E	1.88" (47.6)
F	1.26" (32.0)
G	1.63" (41.4)
H	5.00" (127.0)

