

30A Locking Plugs, Connectors and Receptacles Inches (mm)

UL Type 4, 4X, 6P

IP65, 66, 67, 69k*

SUITABILITY



Rating		Poles/ Wires	Cord Diameter	Color	Thermoplastic elastomer		
Plug	Connector				Plug	Connector	Receptacle
NEMA L5-30, 30A 125V		2-Pole 3-Wire	.385"-.930" (9.8-23.6)	Yellow Black	BRY28W47 BRY28W47BK	BRY29W47 BRY29W47BK	BRY69W47 —
NEMA L6-30, 30A 250V		2-Pole 3-Wire	.385"-.930" (9.8-23.6)	Yellow Black	BRY28W48 —	BRY29W48 —	BRY69W48 BRY69W48BK
NEMA L7-30, 30A 277V		2-Pole 3-Wire	.385"-.930" (9.8-23.6)	Yellow	BRY28W49	BRY29W49	BRY69W49
NEMA L14-30, 30A 125/250V		3-Pole 4-Wire	.385"-.930" (9.8-23.6)	Yellow	BRY28W74	BRY29W74	BRY69W74
NEMA L15-30, 30A 3Ø 250V AC		3-Pole 4-Wire	.385"-.1050" (9.8-26.7)	Yellow Black	BRY28W75 BRY28W75BK	BRY29W75 BRY29W75BK	BRY69W75 BRY69W75BK
NEMA L16-30, 30A 3Ø 480V AC		3-Pole 4-Wire	.385"-.1050" (9.8-26.7)	Yellow Black	BRY28W76 BRY28W76BK	BRY29W76 BRY29W76BK	BRY69W76 BRY69W76BK
NEMA L17-30, 30A 3Ø 600V AC		3-Pole 3-Wire	.385"-.930" (9.8-23.6)	Yellow	BRY28W77	BRY29W77	BRY69W77
NEMA L18-30, 30A 3ØY 120/208V AC		4-Pole 4-Wire	.385"-.1050" (9.8-26.7)	Yellow	BRY28W78	BRY29W78	—
NEMA L21-30 30A 3ØY 120/208V AC		4-Pole 5-Wire	.350"-.1150" (9-29)	Yellow Black	BRY28W81 BRY28W81BK	BRY29W81 BRY29W81BK	BRY69W81 —
NEMA L22-30 30A 3ØY 277/480V AC		4-Pole 5-Wire	.350"-.1150" (9-29)	Yellow	BRY28W82	BRY29W82	BRY69W82
NEMA L23-30 30A 3ØY 347/600V AC		4-Pole 5-Wire	.350"-.1150" (9-29)	Yellow	BRY28W83	BRY29W83	BRY69W83
30A 125/250V, Non-NEMA		3-Pole 3-Wire	.385"-.930" (9.8-23.6)	Yellow	BRY28W08	BRY29W08	BRY69W08
30A 3ØY 120/208V AC, Non-NEMA		4-Pole 4-Wire	.385"-.1050" (9.8-26.7)	Yellow	BRY28W09	BRY29W09	—

Note: *Single receptacles while in use, not with cover closed. Black devices are available, consult factory.
See page I-5 for product dimensions.