

IEC 60309 Pin and Sleeve Devices



Watertight Series North American Ratings

Amps	Poles/Wires	Dual Rated	Ratings	Config-uration	Watertight IP67 Suitability				Back Box*	Closure Cap**
					Inlet	Connector	Plug	Receptacle		
16/20	2P/3W		16A 100-130V		BRY316B4W	BRY316C4W	BRY316P4W	BRY316R4W	BB201WA BB301WA	CC320A
			20A 125V AC		BRY320B4W	BRY320C4W	BRY320P4W	BRY320R4W		
			20A 480V AC		BRY320B7W	BRY320C7W	BRY320P7W	BRY320R7W		
	3P/4W		20A 3Ø 600V		BRY420B5W	BRY420C5W	BRY420P5W	BRY420R5W	BB201WA BB301WA	CC420A
			20A 3Ø 480V		BRY420B7W	BRY420C7W	BRY420P7W	BRY420R7W		
	4P/5W	Dual Rated	16/20A 250VAC		BRY420B9W	BRY420C9W	BRY420P9W	BRY420R9W	BB201WA BB301WA	CC520
			20A 347/600V		BRY520B5W	BRY520C5W	BRY520P5W	BRY520R5W		
		Dual Rated	16/20A 200-415VAC		BRY520B6W	BRY520C6W	BRY520P6W	BRY520R6W		
			20A 277/480V		BRY520B7W	BRY520C7W	BRY520P7W	BRY520R7W		
	Dual Rated	16/20A 120/208V		BRY520B9W	BRY520C9W	BRY520P9W	BRY520R9W			
30/32	2P/3W		32A 100-130V		BRY332B4W	BRY332C4W	BRY332P4W	BRY332R4W	BB201WA BB301WA	CC330
			30A 125V AC		BRY330B4W	BRY330C4W	BRY330P4W	BRY330R4W		
			30A 480V AC		BRY330B7W	BRY330C7W	BRY330P7W	BRY330R7W		
	3P/4W		32A 380-480V		BRY432B3W	BRY432C3W	BRY432P3W	BRY432R3W	BB201WA BB301WA	CC330
			30A 3Ø 600V		BRY430B5W	BRY430C5W	BRY430P5W	BRY430R5W		
		Dual Rated	30/32A 380-415VAC		BRY430B6W	BRY430C6W	BRY430P6W	BRY430R6W		
			30A 3Ø 480V		BRY430B7W	BRY430C7W	BRY430P7W	BRY430R7W		
	4P/5W	Dual Rated	30/32A 3P 250 VAC		BRY430B9W	BRY430C9W	BRY430P9W	BRY430R9W	BB201WA BB301WA	CC530
			30A 347/600V		BRY530B5W	BRY530C5W	BRY530P5W	BRY530R5W		
Dual Rated		30/32A 200-415VAC		BRY530B6W	BRY530C6W	BRY530P6W	BRY530R6W			
		30A 277/480V		BRY530B7W	BRY530C7W	BRY530P7W	BRY530R7W			
	Dual Rated	30/32A 120/208V		BRY530B9W	BRY530C9W	BRY530P9W	BRY530R9W			
60/63	2P/3W		60A 125V AC		BRY360B4W	BRY360C4W	BRY360P4W	BRY360R4W	BB601WA BB602WA	CC560
			60A 480V AC		BRY360B7W	BRY360C7W	BRY360P7W	BRY360R7W		
	3P/4W		60A 3Ø 600V		BRY460B5W	BRY460C5W	BRY460P5W	BRY460R5W		
		Dual Rated	60/63A 380-415VAC		BRY460B6W	BRY460C6W	BRY460P6W	BRY460R6W		
			60A 3Ø 480V		BRY460B7W	BRY460C7W	BRY460P7W	BRY460R7W		
	4P/5W	Dual Rated	60/63A 3P 250 VAC		BRY460B9W	BRY460C9W	BRY460P9W	BRY460R9W		
			60A 347/600V		BRY560B5W	BRY560C5W	BRY560P5W	BRY560R5W		
		Dual Rated	60/63A 200-415VAC		BRY560B6W	BRY560C6W	BRY560P6W	BRY560R6W		
			60A 277/480V		BRY560B7W	BRY560C7W	BRY560P7W	BRY560R7W		
	Dual Rated	60/63A 120/208V		BRY560B9W	BRY560C9W	BRY560P9W	BRY560R9W			

Note: *Back boxes for: 20 and 30 amp receptacles require AP2030 adapter plate (ordered separately). Also see direct mounting back box DM20301 (page K-10) . 60 amp receptacles require AP60 adapter plate (ordered separately). Also see direct mounting back box DM602 (page K-10).

**For use with plugs and inlets. Provides watertight protection.