

IEC 60309 Pin and Sleeve Devices



Watertight 100 Amp North American Ratings

Amps	Poles/Wires	Dual Rated	Ratings	Configuration	Watertight IP67 Suitability				Back Box*	Closure Cap**
					Inlet	Connector	Plug	Receptacle		
100/125	2P/3W		100A 480V AC		BRY3100B7W	BRY3100C7W	BRY3100P7W	BRY3100R7W	BB1001WA BB1002WA	CC510
	3P/4W		100A 3Ø 600V		BRY4100B5W	BRY4100C5W	BRY4100P5W	BRY4100R5W		
		Dual Rated	100/125A 380-415V AC		BRY4100B6W	BRY4100C6W	BRY4100P6W	BRY4100R6W		
			100A 3Ø 480V		BRY4100B7W	BRY4100C7W	BRY4100P7W	BRY4100R7W		
		Dual Rated	100/125A 3P 250 VAC		BRY4100B9W	BRY4100C9W	BRY4100P9W	BRY4100R9W		
	4P/5W		100A 347/600V		BRY5100B5W	BRY5100C5W	BRY5100P5W	BRY5100R5W		
		Dual Rated	100/125A 200-415V AC		BRY5100B6W	BRY5100C6W	BRY5100P6W	BRY5100R6W		
			100A 277/480V		BRY5100B7W	BRY5100C7W	BRY5100P7W	BRY5100R7W		
		Dual Rated	100/125A 120/208V		BRY5100B9W	BRY5100C9W	BRY5100P9W	BRY5100R9W		

Watertight International Ratings

Amps	Poles/Wires	Dual Rated	Ratings	Configuration	Watertight IP67 Suitability				Back Box*	Closure Cap**
					Inlet	Connector	Plug	Receptacle		
16/20	2P/3W		16A 100-130V		BRY316B4W	BRY316C4W	BRY316P4W	BRY316R4W	BB201WA BB301WA	CC320A
	3P/4W	Dual Rated	16/20A 3P 250 VAC		BRY420B9W	BRY420C9W	BRY420P9W	BRY420R9W	BB201WA BB301WA	CC420A
	4P/5W	Dual Rated	16/20A 200-415V AC		BRY520B6W	BRY520C6W	BRY520P6W	BRY520R6W	BB201WA BB301WA	CC330
		Dual Rated	16/20A 120/208V		BRY520B9W	BRY520C9W	BRY520P9W	BRY520R9W		
30/32	2P/3W		32A 100-130V		BRY332B4W	BRY332C4W	BRY332P4W	BRY332R4W	BB201WA BB301WA	CC330
	3P/4W		32A 380-480V		BRY432B3W	BRY432C3W	BRY432P3W	BRY432R3W		
		Dual Rated	30/32A 380-415V AC		BRY430B6W	BRY430C6W	BRY430P6W	BRY430R6W		
		Dual Rated	30/32A 3P 250 VAC		BRY430B9W	BRY430C9W	BRY430P9W	BRY430R9W		
	4P/5W	Dual Rated	30/32A 200-415V AC		BRY530B6W	BRY530C6W	BRY530P6W	BRY530R6W	BB201WA BB301WA	CC530
		Dual Rated	30/32A 120/208V		BRY530B9W	BRY530C9W	BRY530P9W	BRY530R9W		
60/63	3P/4W	Dual Rated	60/63A 380-415V AC		BRY460B6W	BRY460C6W	BRY460P6W	BRY460R6W	BB601WA BB602WA	CC560
		Dual Rated	60/63A 3P 250 VAC		BRY460B9W	BRY460C9W	BRY460P9W	BRY460R9W		
	4P/5W	Dual Rated	60/63A 200-415V AC		BRY560B6W	BRY560C6W	BRY560P6W	BRY560R6W		
		Dual Rated	60/63A 120/208V		BRY560B9W	BRY560C9W	BRY560P9W	BRY560R9W		

Note: *Back boxes for: 16 and 32 amp receptacles require AP2030 adapter plate (ordered separately). Also see direct mounting back box DM20301. 63 amp receptacles require AP60 adapter plate (ordered separately). Also see direct mounting back box DM602. 125 amp receptacles require AP100 adapter plate ordered separately (page K-10).
 **For use with plugs and inlets. Provides watertight protection.