

IEC 60309 Pin and Sleeve Devices



Splashproof Series North American Ratings

Amps	Poles/Wires	Dual Rated	Ratings	Configu-ration	Splashproof IP44 Suitability				Back Box*	Closure Cap**	
					Inlet	Connector	Plug	Receptacle			
16/20	2P/3W	Dual Rated	16A 100-130V		BRY316B4S	BRY316C4S	BRY316P4S	BRY316R4S	BB201WA BB301WA	CC320A	
			20A 125V AC		BRY320B4S	BRY320C4S	BRY320P4S	BRY320R4S			
			20A 480V AC		BRY320B7S	BRY320C7S	BRY320P7S	BRY320R7S			
	3P/4W	Dual Rated	20A 3Ø 600V		BRY420B5S	BRY420C5S	BRY420P5S	BRY420R5S	BB201WA BB301WA	CC420A	
			20A 3Ø 480V		BRY420B7S	BRY420C7S	BRY420P7S	BRY420R7S			
			16/20A 3P 250 VAC		BRY420B9S	BRY420C9S	BRY420P9S	BRY420R9S			
	4P/5W	Dual Rated	20A 347/600V		BRY520B5S	BRY520C5S	BRY520P5S	BRY520R5S	BB201WA BB301WA	CC520	
			16/20A 200-415V AC		BRY520B6S	BRY520C6S	BRY520P6S	BRY520R6S			
			20A 277/480V		BRY520B7S	BRY520C7S	BRY520P7S	BRY520R7S			
			16/20A 120/208V		BRY520B9S	BRY520C9S	BRY520P9S	BRY520R9S			
	30/32	2P/3W	Dual Rated	32A 100-130V		BRY332B4S	BRY332C4S	BRY332P4S	BRY332R4S	BB201WA BB301WA	CC330
				30A 125V AC		BRY330B4S	BRY330C4S	BRY330P4S	BRY330R4S		
30A 480V AC					BRY330B7S	BRY330C7S	BRY330P7S	BRY330R7S			
3P/4W		Dual Rated	32A 380-480V		BRY432B3S	BRY432C3S	BRY432P3S	BRY432R3S	BB201WA BB301WA	CC330	
			30A 3Ø 600V		BRY430B5S	BRY430C5S	BRY430P5S	BRY430R5S			
			30/32A 380-415V AC		BRY430B6S	BRY430C6S	BRY430P6S	BRY430R6S			
			30A 3Ø 480V		BRY430B7S	BRY430C7S	BRY430P7S	BRY430R7S			
4P/5W		Dual Rated	30A 347/600V		BRY530B5S	BRY530C5S	BRY530P5S	BRY530R5S	BB201WA BB301WA	CC530	
			30/32A 200-415V AC		BRY530B6S	BRY530C6S	BRY530P6S	BRY530R6S			
			30A 277/480V		BRY530B7S	BRY530C7S	BRY530P7S	BRY530R7S			
			30/32A 120/208V		BRY530B9S	BRY530C9S	BRY530P9S	BRY530R9S			
60/63		2P/3W	Dual Rated	60A 125V AC AC		BRY360B4S	BRY360C4S	BRY360P4S	BRY360R4S	BB601WA BB602WA	CC560
	60A 480V AC AC				BRY360B7S	BRY360C7S	BRY360P7S	BRY360R7S			
	3P/4W	Dual Rated	60A 3Ø 600V		BRY460B5S	BRY460C5S	BRY460P5S	BRY460R5S			
			60/63A 380-415V AC		BRY460B6S	BRY460C6S	BRY460P6S	BRY460R6S			
			60A 3Ø 480V		BRY460B7S	BRY460C7S	BRY460P7S	BRY460R7S			
			60/63A 3P 250 VAC		BRY460B9S	BRY460C9S	BRY460P9S	BRY460R9S			
	4P/5W	Dual Rated	60A 347/600V		BRY560B5S	BRY560C5S	BRY560P5S	BRY560R5S			
			60/63A 200-415V AC		BRY560B6S	BRY560C6S	BRY560P6S	BRY560R6S			
			60A 277/480V		BRY560B7S	BRY560C7S	BRY560P7S	BRY560R7S			
			60/63A 120/208V		BRY560B9S	BRY560C9S	BRY560P9S	BRY560R9S			

Note: *Back boxes for: 20 and 30 amp receptacles require AP2030 adapter plate (ordered separately). Also see direct mounting back box DM20301. 60 amp receptacles require AP60 adapter plate (ordered separately). Also see direct mounting back box DM602 (page K-10).
 **For use with plugs and inlets. Provides watertight protection.