

Power Distribution Boxes



Temporary Power Boxes, Cable Sets and Replacement Parts



- Weatherproof receptacle lift covers
- Available with six 20A straight blade or locking receptacles
- Features 50A locking input and output
- Over current protection for each circuit
- Individual GFCI module for each receptacle
- Nested leg design allows boxes to be easily stacked
- UL Type 3R for outdoor rainproof applications

Temporary Power Distribution Boxes

| Rating | Type | Qty | Receptacle Ratings | Protection Overload | GFCI Protected | Catalog Number |
|------------------------|------------------|-----|--------------------|---------------------|----------------|----------------|
| 50A 120/240V AC (Max.) | Straight Blade | 6 | 20A 125V | Yes | Yes | TPDSB |
| | Locking | 1 | 30A 250V | Yes | No | |
| | Locking (inlet) | 1 | 50A 125/250V | No | No | |
| | Locking (outlet) | 1 | 50A 125/250V | No | No | |
| 50A 120/240V AC (Max.) | Locking | 6 | 20A 125V | Yes | Yes | TPDLB |
| | Locking | 1 | 30A 250V | Yes | No | |
| | Locking (inlet) | 1 | 50A 125/250V | No | No | |
| | Locking (outlet) | 1 | 50A 125/250V | No | No | |

Cable Sets



TPC50B

| Description | 50 Ft. Cable | 100 Ft. Cable |
|---|----------------|-----------------|
| 50A cord set, #6/3, #8/1 cable type, with 50A locking plug and connector. | TPC50B* | TPC100B* |

Note: * Not UL Listed or CSA Certified.

Replacement Parts



| Description | 20A 125V | 30A 250V | 50A 125/250V |
|---|----------------|----------------|----------------|
| Straight blade receptacle | 5361BLK | — | — |
| Locking receptacle | 70520FR | 70630FR | CS6369L |
| Plug | — | — | CS6365L |
| Connector | — | — | CS6364L |
| Inlet | — | — | CS6375L |
| Weather protective plate for receptacle | — | — | 7774CR |
| Weather protective plate for inlet | — | — | 7780 |

Product Dimensions Inches (mm)

| TPD Box | |
|---------|----------------|
| A | 12.52" (317.9) |
| B | 10.23" (259.8) |
| C | 14.50" (368.3) |
| D | 21.50" (546.1) |

