

# Temporary Lighting

## Construction Site Lighting



Bryant's outdoor approved construction site lighting line includes both heavy-duty metal halide lights and light strings for working in rugged environments. The metal halide fixtures feature extremely strong and compact heads with bulbs rated to last 10,000 hours. All frames are powder-coated yellow for safety and are constructed of a durable 1.25 inch, 12 gauge steel tube.

Light strings for all applications are available in a variety of models as well as a choice of metal or plastic guards. Light sockets are spaced 10 feet apart and all sockets, plugs, and connectors are molded for added durability. In addition, the highly impact-resistant material makes for easy transportation and storage when not in use. Bulbs can be incandescent, fluorescent or LED. Consider choosing LED lighting for a durable bulb that saves energy, provides instant illumination and are rated to last 50,000 hours.



**BRYMHHB400**

### Metal Halide and LED Lights

Description	Rating	Watts	Lumen Output	Cord Length	Catalog Number
High bay metal halide light with wire guard.	15A 125V	400	29,000	3 ft.	<b>BRYMHHB400</b>
High bay LED light with wire guard.	15A 125V	120	14,000	5 ft.	<b>BRYLEDHB120</b>
	15A 125V	100	12,000	5 ft.	<b>BRYLEDHB100</b>
	15A 125V	60	7,200	5 ft.	<b>BRYLEDHB60</b>



**BRYLEDHB120**

### LED Stringer Lights

Description	No. of Fixtures	Rating	Cord Type	Lumen Output	Cord Length	Catalog Number
90 LEDs per fixture, light string with magnetic base included.	1	15A 125V	#18/2 SJTW	450*	20 ft.	<b>BRY182S20LED</b>
90 LEDs per fixture, light string.	5	15A 125V	#18/2 SJTW	450*	50 ft.	<b>BRY182S50LED</b>
	10	15A 125V	#18/2 SJTW	450*	100 ft.	<b>BRY182S100LED</b>
Magnetic clip bracket for LED light string.						<b>BRYSTMC</b>

Note: \*Lumens per fixture.



**BRY182S50LEDH**

### A Type (Edison) Locking and Straight Blading Light Strings

Description	Max Watts**	Rating	Cord Type	Fixtures	Cord Length	Catalog Number
Locking light string; plastic guards.	150	20A 125V	#12/3 STJW	10	100 ft.	<b>BRY123SJ100PT</b>
Straight Blade light string; plastic guards.	150	15A 125V	#14/2 STJW	10	100 ft.	<b>BRY142SJ100PS</b>
	150	15A 125V	#12/3 STW	10	100 ft.	<b>BRY123S100PS</b>
	150	15A 125V	#12/3 STJW	10	100 ft.	<b>BRY123SJ100PS</b>
Straight Blade light string; metal guards.	150	15A 125V	#12/3 STW	10	100 ft.	<b>BRY123S100MS</b>
Straight Blade light string; plastic guards.	150	15A 125V	#12/3 STW	5	50 ft.	<b>BRY123S50PS</b>
Straight Blade light string; metal guards.	150	15A 125V	#12/3 STW	5	50 ft.	<b>BRY123S50MS</b>
Replacement plastic guard for temporary light strings.						<b>BRYSTPG</b>
Replacement heavy duty metal guard for temporary light strings.						<b>BRYSTMG</b>

Note: \*\*Max watts per fixture. The total wattage must be considered when daisy chaining lights strings to each other.



**BRY142SJ100PS**



**BRYSTMC**



**BRYSTPG**



**BRYSTMG**