

Electric Cord and Cable Reels

inREACH™ Industrial Cord Reels



- Durable, corrosion resistant cast aluminum construction
- White powder coat finish
- Multi-position guide arm can be mounted in two positions
- Positive latch mechanism automatically maintains desired cord length
- Ratchet lock can be disengaged in field for constant tension applications
- 16–10 AWG, 3 & 4 conductor cord for greater current carrying capacity
- Available in 45ft lengths

inREACH™ Industrial Cord Reels Connector Ends

Description	Amps	Volts AC	Cable Length Feet (m)	Cable Type	Weight Lbs. (kg)	Catalog Number
White Industrial Reel with HBL5269C	15	125	45 (13.7)	14/3 SJO	24.0 (10.9)	BRYI45143C15
White Industrial Reel with HBL5369C	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	BRYI45123C20
White Industrial Reel with (1) 15A Duplex Receptacle Yellow Portable Outlet Box (2) 15A Duplex Receptacles	15	125	45 (13.7)	14/3 SJO	26.5 (12.0)	BRYI45143R15 BRYI45143R215
GFCI Module and (1) 15A Duplex Receptacle	15	125	45 (13.7)	14/3 SJO	26.5 (12.0)	BRYI45143GF15
White Industrial Reel with (1) 20A Duplex Receptacle Yellow Portable Outlet Box (2) 20A Duplex Receptacles	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	BRYI45123R20 BRYI45123R220
GFCI Module and (1) 20A Duplex Receptacle	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	BRYI45123GF20
GFCI Module and (2) 20A Duplex Receptacles	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	BRYI45123GF220
Mounting bracket					2.5 (1.1)	BRYIMB
340° pivot base					3.5 (1.1)	BRYI340PB

Note: 15A reels are supplied with HBL5266C on the power supply cord. 20A reels are supplied with HBL5366C on the power supply cord.



HBLI45143C15



HBLI45123R20



HBLI45123GF20



HBLIMB

Commercial Cord Reels



BRYC40123TT

BRYC25163C

- Steel and heavy duty non-metallic design for commercial and general purpose applications
- Molded on plug for power cord requires no electrical wiring
- Compact size takes up little room and can be ceiling, wall or bench mounted
- Automatic ratchet lock holds cord at desired length and provides easy, smooth retraction of cord

Commercial Cord Reels, Feet (m)

Description	Cable Feet (m)	Cable Type	Watts (Max)	Amps Volts	Weight Lbs. (kg)	Catalog Number
Triple tap outlet, black	40 (12.2)	12/3 SJTW	1,875	15A 125V AC	9.0 (4.1)	BRYC40123TT
5-15R connector, yellow	25 (7.6)	16/3 SJT	1,250	10A 125V AC	8.5 (3.9)	BRYC25163C

Note: Reels supplied with 2 ft. power supply cord and molded on straight blade 15A plug.

Product Dimensions Inches (mm)

	Triple Tap	5-15R Connector
A	15.51" (394.6)	9.50" (241)
B	30.0" (762.0)	11.38" (289)
C	5.26" (133.84)	4.11" (104)
D	3.75" (95.4)	2.83" (72)
E	4.19" (106.6)	–

Product Dimensions Inches (mm)

Industrial Reel	
A	13.00" (330)
B	12.38" (314)
C	8.00" (203)
D	2.50" (64)
E	9.75" (248)
F	1.25" (32)

