

Lampholders, Starters and Adapters



Incandescent Lampholders

HID Incandescent Lampholders, Porcelain Keyless



Catalog Number	RL4221*	RL5221	RL3742	3743R
Description	Mogul base	Mogul base	Medium base prefocus, porcelain, white	Medium base, thermoplastic, black
Lamp Type	E39 socket	EX39 socket	Bayonet socket	Bayonet HID socket
Rating	1500W 600V Max, 4KV or 5KV PULSE	1500W 600V Max, 5KV PULSE	1200W 250V	1000W 250V
Mounting	Screw mount, 12 inch leads	Screw mount, 12 inch leads	Screw mount	Screw mount

Note: *UL Listed, CSA Certified.

Straight Body, Porcelain Keyless



Catalog Number	RL162	RL156	RL157	RL160	RL158	RL159
Description	Medium base	Medium base	Medium base	Medium base	Medium base, low profile	Medium base, shallow base
Lamp Type	E26 socket	E26 socket	E26 socket	E26 socket	E26 socket	E26 socket
Rating	660W 250V	660W 250V	660W 250V	660W 250V	660W 250V	660W 250V
Mounting	Screw mount, screw terminals	Screw mount, 12 inch leads	NPSF1/8 hickey with terminals	NPSF1/8 hickey with 12 inch leads	Front panel mount, snap-in	Front panel mount, snap-in

Surface and Sign Mount, Medium Base



Catalog Number	RL152	RL153	RL161	RL163	RL164
Description	Medium base, porcelain, pony cleat	Medium Base, plastic, black, pony cleat	Medium base, porcelain	Medium base, porcelain	Medium base, porcelain
Lamp Type	E26 socket	E26 socket	E26 socket	E26 socket	E26 socket
Rating	660W 600V	660W 250V	660W 250V	660W,250V	660W 250V
Mounting	1 piece, surface mount	1 piece, surface mount	2 piece, surface mount	2 piece, sign mount with leads	2 piece, sign mount with terminals

Product Dimensions Inches (mm)

