

Delivery Systems

Aluminum Service Poles

Aluminum Series Offering

Bryant offers a line of gray, ivory and clear anodized aluminum service poles. These attractive and durable poles effectively distribute power and telecommunications wiring from above the ceiling to workstations below. They are offered in lengths of 10' 2", 12' 2", and 15' 2" with a variety of electrical wiring devices. Poles with three service capability have a divider to separate power and low voltage wiring.

A blank pole with knockouts is also offered which does not have devices or wiring. In addition to a standard pole, which has two 20 amp duplex receptacles, an isolated ground or surge suppression version is also available. All poles, except the blank versions, are factory wired with Bryant Decorator Receptacles. Two decorator knockouts are also provided on the same side as the power receptacles for communication outlets.



Ordering Information Feet (m)

Aluminum service poles, gray or ivory painted and clear anodized aluminum, decorator duplex receptacles and two decorator knockouts for communications, includes ceiling trim mounting plate and scuff boot.

Description	Height	Catalog Number		Clear Anodized Aluminum
		Gray	Ivory	
Three service, two 20A 125V decorator duplex receptacles, one circuit	10' 2" (3.10)	BRYPP10A	BRYPP10AI	BRYPP10AAL
	12' 2" (3.71)	BRYPP12A	BRYPP12AI	BRYPP12AAL
	15' 2" (4.62)	BRYPP15A	BRYPP15AI	BRYPP15AAL
Three service, one orange isolated ground 20A 125V decorator duplex receptacle, one 20A 125V decorator duplex receptacle, two circuits	10' 2" (3.10)	BRYPP10IGA	BRYPP10IGAI	—
Three service, two orange isolated ground 20A 125V decorator duplex receptacles, one isolated ground surge suppression 20A 125V duplex receptacle, one circuit	10' 2" (3.10)	BRYPP10SA	BRYPP10SAI	—
Three service, blank pole, divider, four decorator device knockouts	10' 2" (3.10)	BRYPP0A	BRYPP0AI	BRYPP0AAL
	12' 2" (3.71)	BRYPP012A	BRYPP012AI	BRYPP012AAL
	15' 2" (4.62)	BRYPP015A	BRYPP015AI	BRYPP015AAL
Adjustable T-bar assembly for mounting poles in the middle of ceiling tile		BRYATB	BRYATB	BRYATB
Replacement service pole trim kit (office white)		BRYPPTRIM1	BRYPPTRIM1	BRYPPTRIM1

Note: See Network Wiring Section Q for additional information on datacom products.

Specifications Inches (mm)

Material: Extruded aluminum, 0.05" (1.27mm) thick
 Finish: Gray, ivory or clear anodized aluminum
 Conductors: #12 AWG stranded copper

Receptacles: (see drawings below)
 Listing: UL Listed

Wiring Capacity (@40% fill)	Voice Data Channel*			Power Channel**
	Cat. 5e	Cat. 6	Cat. 6A	
BRYPP10A, BRYPP12A, BRYPP15A: BRYPP10IGA	26	11	9	41
BRYPP10SA, BRYPP10SAI	8	6	3	41
BRYPP0A, BRYPP012A, BRYPP015A (with barrier)	26	11	9	41

Note: *Pole wiring capacity (telephone fill): Cat. 5 UTP (1.96 sq. ft.).
 **#12 THHN stranded.

Product Dimensions Inches (mm)

