

Wallplates and Covers

Specialty Wallplates and Accessories

Oil and Gas Burner Emergency Wallplates Inches (mm)

Description	Color/Material	Oil Burner Cover	Gas Burner Cover	Emergency Cover
1-Gang, 1-Toggle, in. (6.4) silk screened white letters	Red Enameled Steel	S22710EM	S2271GEM	—
Utility/handy box cover, 1-Toggle, in. (6.4) silk screened white letters	Red Enameled Steel	SY865OEM	SY865GEM	SY865EM
4 in. (101.6) square box cover, 1-Toggle, in. (6.4) silk screened white letters	Red Enameled Steel	SY800OEM	SY800GEM	—
4 in. (101.6) square box cover, 2-Toggle, in. (6.4) silk screened white letters	Red Enameled Steel	—	SY803GEM	—

Wallplate Screws, 6-32 Thread, 100 Count

Description	Color/Material	Decorator 3/8 in. Long	Standard 1/2 in. Long	Standard 5/8 in. Long	Standard 1.0 in. Long
Wallplate screws, oval head milled slot, 6-32 thread, 100 per box (order 1 to receive a box of 100)	Black	RA38BKPK100	RA12BKPK100	—	—
	Brown	RA38PK100	RA12PK100	—	—
	Gray	RA38GYPK100	RA12GYPK100	—	—
	Ivory	RA38IPK100	RA12IPK100	—	RA88IPK100
	Light Almond	RA38LAPK100	RA12LAPK100	—	—
	White	RA38WPK100	RA12WPK100	—	RA88WPK100
	Stainless Steel	RA38SSPK100	—	RA58SSPK100	RA88SSPK100

Accessories Inches (mm)

Color	To Fill a Toggle Opening	To Fill a Decorator Opening	0.406 in. (10.30) Dia. Hole, To Fill a Decorator Opening	Material	Mounting Strap, with Screws	Brass Plated Screw, Standard Slot, 0.38 in. (9.7) long
Brown	RA756	—	—	Steel	RA40	—
Black	—	NS620BK	—	Brass	—	HBL7341
Gray	—	NS620GY	—			
Ivory	RA756I	NS620I	NS621I			
Light Almond	—	NS620LA	NS621LA			
White	RA756W	NS620W	NS621W			

Tamperproof Wallplate Screws and Screwdriver* Inches (mm)

Description	Length in. (mm)	Spanner Head Type 6-32 Thread	Spanner Head Screwdriver	Replacement Barrel Key
Spanner head stainless steel type 302/304, 6-32 thread, screws sold in carton quantities of 100	1/4 in. (3.2)	SSTP14	SSTPD	6006RKL
	3/8 in. (9.5)	SSTP38		
	1/2 in. (12.7)	SSTP12		
	5/8 in. (15.9)	SSTP58		
	1 in. (25.4)	SSTP1		
	2 in. (50.8)	SSTP2		

Note: * Not UL Listed or CSA Certified.