


Wallplates and Covers




Single Receptacle Wallplates

Single 20/30A Locking Receptacle Wallplates

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
	1-Gang, 1-Single, 1.60 in. (40.6) Dia. Hole	Black P720BK	—	Aluminum	—
		Brown P720	—	Brass	SB720
		Gray P720GY	—	Brass Plated	①
		Ivory P720I	—	Chrome	①
		Red P720R	—	S/S 302/304	SS720
	1-Gang, 1-Single, 1.74 in. (44.2) Dia. Hole	White P720W	—	Aluminum	—
				Brass	—
				Brass Plated	—
				Chrome	—
				S/S 302/304	SS725
	2-Gang, 1-Single, 1.60 in. (40.6) Dia. Hole			Aluminum	—
				Brass	—
				Brass Plated	—
				Chrome	—
				S/S 302/304	SS749
	3-Gang, 2-Single, 1.60 in. (40.6) Dia. Hole			Aluminum	①
				Brass	①
				Brass Plated	①
				Chrome	①
				S/S 302/304	SS320

Single Receptacle Wallplates

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
	1-Gang, 1-Single, 1.97 in. (50.0) Dia. Hole			Aluminum	—
				Brass	—
				Chrome	—
				S/S 302/304	SS737
	1-Gang, 1-Single, 2.16 in. (54.9) Dia. Hole	Black P724BK	PJ724BK	Aluminum	—
		Ivory P724I	PJ724I	Brass	①
		White P724W	PJ724W	Brass Plated	①
				Chrome	SCH723
				S/S 302/304	SS723
	2-Gang, 1-Single, 2.16 in. (54.9) Dia. Hole			Aluminum	—
				Brass	—
				Chrome	—
				S/S 302/304	SS702
	2-Gang, 1-Single, 2.16 in. (54.9) Dia. Hole	Black P703BK	PJ703BK	Aluminum	—
		Ivory P703I	PJ703I	Brass	—
		White P703W	PJ703W	Brass Plated	—
				Chrome	—
				S/S 302/304 S/S 430	SS703 SS703L
	2-Gang, 1-Single, 2.48 in. (63.0) Dia. Hole			Aluminum	—
				Brass	—
				Chrome	—
				S/S 302/304	SS701
	2-Gang, 1-Single, 2.66 in. (67.6) Dia. Hole			Aluminum	—
				Brass	—
				Chrome	—
				S/S 302/304	SS716

Note: Thermoplastic wallplates feature pre-inserted captive screws for faster assembly in single gang configurations.

① Available as a custom wallplate, see pages Q-29 & Q-30. Consult custom wallplates section for additional openings and combinations.