

### TYPE CS3CO-B

#### Cold Shrink Medium Voltage Termination Kits 3 Conductor Conversion Series - Indoor/Outdoor Sleeves with Boot for up to 35kV Applications

Designed to be used with BURNDY Single Conductor Accessories on Three-Conductor Cables, for 5–35 kV applications

Material: Silicone Rubber

Type CS3CO-B Series of 3 Conductor Conversion Kits with Breakout Boot are designed to be used with single conductor, Indoor and Outdoor Cable Accessories on three-conductor (3/C) cables. The Breakout Kit is easy and quick to install, even in confined spaces – with no special tools, torch/flame or hot permits required. The BURNDY Type CS3CO-B series with breakout boot conforms to IEEE-48-2009, Class 1 and ISO/IEC 17025 Standards. Test Reports available on request. Please order one kit per three conductor cable application.

#### Kit Contents includes:

- (1) Cold Shrink Silicone Rubber Breakout Boot
- (4) Strips of Mastic Tape
- (3) Silicone Rubber Re-jacketing Sleeves
- (1) Long Tail Tinned Copper Ground Braid with Solder Block (for Armored Cable Only)
- (1) Large Constant Force Spring
- (1) Roll Black Electrical Tape
- (1) Roll Electrical Shielding (Mesh) Tape
- (1) Cable Tie
- (1) Cable Prep Kit

Shown with  
Single Conductor Termination Kit  
(sold separately)



#### Features and Benefits

- Grip and Rip! Does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core; Rip cord is recyclable
- All kits supplied with cold shrinkable tube (unprinted), 3-leg boot, seal, cable tie, and installation guide
- Quick, easy, cost effective installation utilizing one-piece terminator design
- Test reports available upon request

Outdoor (Skirted) Catalog Number	kV Rating	Rip Cord I.D.	Sleeve Range	Cable Insulation Outside Diameter Range
CS3CO58220B	5 - 8	1.33	2 - 2/0	0.61 - 0.82
CS3CO5820350B		1.60	2/0 - 350	0.72 - 1.10
CS3CO585001000B		1.60	500 - 1000	1.08 - 1.45
CS3CO15210B	15	1.33	2 - 1/0	0.74 - 0.96
CS3CO1510350B		1.60	1/0 - 350	0.80 - 1.27
CS3CO15500750B		1.60	500 - 750	1.23 - 1.52
CS3CO2528140B	25 - 28	1.60	1 - 4/0	0.80 - 1.27
CS3CO2528250500B		2.19	250 - 500	1.10 - 1.52
CS3CO2835140B	28 - 35	2.19	1 - 4/0	0.80 - 1.27
CS3CO2835250500B		2.43	250 - 500	1.10 - 1.52