

Straight Blade Devices



Commercial Grade Duplex Receptacles



- Self-grounding staple
- Impact resistant molded nylon face and base
- Sturdy construction with wrap-around galvanized steel strap
- Thread cleaning, captive mounting screws
- Easy access break-off tab for two-circuit wiring
- Tri-drive steel binding head terminal screws accept up to #10 AWG
- Double-wipe ground contact
- Eight wiring pockets with clamp-type terminals on back-wired devices
- Backed-out green tri-drive grounding screw
- One piece brass line contacts
- UL, CSA, Fed-Spec® and NOM (Fed. Spec. on CBRS devices only)

15A and 20A 125V Self-Grounding Receptacles




Wiring		Side Wired		Back and Side Wired	
Rating	Color	Duplex	Isolated Ground	Duplex*	Decorator
NEMA 5-15, 15A 125V 	Black	CRS15BLK	—	CBRS15BLK	DRS15BLK
	Brown	CRS15	—	CBRS15	DRS15
	Gray	CRS15GRY	CR15IGRY	CBRS15GRY	DRS15GRY
	Ivory	CRS15I	CR15IGI	CBRS15I	DRS15I
	Light Almond	CRS15LA	—	CBRS15LA	DRS15LA
	Orange	—	CR15IG	—	—
White	CRS15W	CR15IGW	CBRS15W	DRS15WHI	
NEMA 5-20, 20A 125V 	Black	CRS20BLK	—	CBRS20BLK	DRS20BLK
	Brown	CRS20	—	CBRS20	DRS20
	Gray	CRS20GRY	CR20IGRY	CBRS20GRY	DRS20GRY
	Ivory	CRS20I	CR20IGI	CBRS20I	DRS20I
	Light Almond	CRS20LA	—	CBRS20LA	DRS20LA
	Orange	—	CR20IG	—	—
White	CRS20W	CR20IGW	CBRS20W	DRS20WHI	


Note: See Section C for isolated ground products.
*Fed. Spec. Listed.

Product Dimensions Inches (mm)


	Duplex	Decorator	Tamper-Resistant	Weather Resistant	Tamper-Resistant, Weather Resistant	Decorator, Nightlight
A	4.06" (103.1)	4.06" (103.1)	4.06" (103.1)	4.06" (103.1)	4.06" (103.1)	4.14" (105.1)
B	3.28" (83.3)	3.28" (83.3)	3.28" (83.3)	3.28" (83.3)	3.28" (83.3)	3.28" (83.3)
C	1.38" (35.1)	—	1.38" (35.1)	1.38" (35.1)	1.38" (35.1)	1.29" (32.7)
D	1.07" (27.1)	1.07" (27.1)	1.15" (29.2)	1.17" (29.7)	1.15" (29.2)	1.15" (29.2)
E	2.73" (69.4)	2.73" (69.4)	2.73" (69.4)	2.73" (69.4)	2.73" (69.4)	2.73" (69.4)



Duplex



Decorator



Nightlight