

# Straight Blade Devices



## TECH-SPEC® Plugs and Connectors

15A and 20A 125V and 250V Plugs and Connectors, 2-Pole 3-Wire Inches (mm)



Device Type	Plug			Connector	
	Standard	Watertight	Angle 12 Position	Standard	Watertight
Cord Diameter	.245"-.655" (6.2-16.6)	.300"-.655" (7.6-16.6)	.300"-.655" (7.6-16.6)	.245"-.655" (6.2-16.6)	.300"-.655" (7.6-16.6)
Rating	Thermoplastic	Elastomeric	Nylon	Thermoplastic	Elastomeric
NEMA 5-15, 15A 125V	Black 5266B Gray 5266BGRY Yellow 5266BY Black/White — Hi-Viz Green 5156HVG* Hi-Viz Orange 5156HVO*	BRY14W47BK — BRY14W47 —	— — — 5295	5269B — 5269BY —	— — BRY15W47 —
NEMA 5-20, 20A 125V	Black 5364B Gray — Yellow 5364BY Black/White —	— — BRY14W33 —	— — — 5395	5369B — 5369BY —	— — BRY15W33 —
NEMA 6-15, 15A 250V	Yellow — Black/White — Black 5666B	BRY14W49 —	— 5695	— — 5669B	BRY15W49 — —
NEMA 6-20, 20A 250V	Yellow — Black/White — Black 5464B	BRY14W48 —	— 5475N	— — 5469B	BRY15W48 — —

Note: \*Hi-Viz green and orange devices are shipped in a display pack.

## Weather Protective Accessories



		Weather Protective Boots		Sealing Ring
Material	Color	For Use with 5266B Series Plug	For Use with 5269B Series Connector	For Use with 5200BC Series Connector Boot
Thermoplastic	Black	5200BPB**	5200BCB**	5200BSRB**
elastomer	Yellow	5200BP**	5200BC**	5200BSR**

Note: \*\*Not UL Listed or CSA Certified.

## Product Dimensions Inches (mm)

	Plug		
	Standard	Watertight	Angled Plug
A	1.53" (38.9)	—	1.25" (31.8)
B	2.10" (53.3)	3.16" (80.3)	2.07" (52.6)
C	1.38" (35.1)	1.85" (47.1)	—

  

	Connector	
	Standard	Watertight
A	1.53" (38.9)	—
B	2.68" (68.1)	4.42" (112.1)
C	1.38" (35.1)	1.85" (47.1)

