

Straight Blade Devices



Industrial Grade Extra Heavy Duty, Specification Grade Duplex Receptacles



- Nylon construction with Circuit ID marking area
- Heavy duty nickel and brass plated steel wrap-around yoke
- Heavy duty, copper-alloy self-grounding system
- UL Listed, CSA Certified, Complies with NEMA® Standards WD-1 and WD-6, Listed to UL 498, Verified under Federal Specification WC596

The BRY5362 Design

The one-piece ground system provides a more reliable continuity to ground than riveted designs. Triple-wipe brass line contacts deliver excellent conductivity for low resistance, low heat rise. Superior spring properties provide reliable, long-life blade retention. All nylon, wrap-around, full-face design provides secure assembly, even under stress.

15A and 20A 125V and 250V Receptacles, Back and Side Wired



Rating	Color	Duplex		Color	Isolated Ground		Color	Corrosion Resistant
		Standard	Weather Resistant		Standard	Weather Resistant		Standard
NEMA 5-15, 15A 125V 	Black	BRY5262BLK	BRY5262BLKWR	Brown Gray Ivory Orange White	BRY5262IGB	—	Brown Yellow	BRY5262BCR
	Blue	BRY5262BU	BRY5262BUWR		BRY5262IGGRY	BRY5262IGGRYWR		BRY5262CR
	Brown	BRY5262	BRY5262WR		BRY5262IGI	BRY5262IGIWR		
	Gray	BRY5262GRY	BRY5262GRYWR		BRY5262IG	BRY5262IGWR		
	Ivory	BRY5262I	BRY5262IWR		BRY5262IGW	BRY5262IGWWR		
	Red	BRY5262RED	BRY5262REDWR					
NEMA 5-20, 20A 125V 	Black	BRY5362BLK	BRY5362BLKWR	Brown Gray Ivory Orange White	BRY5362IGB	—	Yellow	BRY5362CR
	Blue	BRY5362BU	BRY5362BUWR		BRY5362IGGRY	BRY5362IGGRYWR		
	Brown	BRY5362	BRY5362WR		BRY5362IGI	BRY5362IGIWR		
	Gray	BRY5362GRY	BRY5362GRYWR		BRY5362IG	BRY5362IGWR		
	Ivory	BRY5362I	BRY5362IWR		BRY5362IGW	BRY5362IGWWR		
	Red	BRY5362RED	BRY5362REDWR					
NEMA 6-15, 15A 250V 	Black	BRY5662BLK	—	Orange	BRY5662IG	—	Yellow	BRY5662CR
	Brown	BRY5662	—					
	Gray	BRY5662GRY	—					
	Ivory	BRY5662I	—					
	Red	BRY5662RED	—					
	White	BRY5662W	—					
NEMA 6-20, 20A 250V 	Black	BRY5462BLK	—	Orange	BRY5462IG	—	Yellow	BRY5462CR
	Brown	BRY5462	—					
	Gray	BRY5462GRY	—					
	Ivory	BRY5462I	—					
	Red	BRY5462RED	—					
	White	BRY5462W	—					

Note: See page R-6 for weather resistant description. See page A-28 for technical specifications.

See Section C for isolated ground products. See page R-6 for weather resistant description.

See Section I for corrosion-resistant products.

15A and 20A 125V Specialty Receptacles

Inches (mm)

Rating	Description	Color	Catalog Number
NEMA 5-15, 15A 125V	BRY5262 on 4.0" (101.6) round metal box cover	Brown	BRY5282
NEMA 5-20, 20A 125V	BRY5362 on 4.0" (101.6) round metal box cover	Brown	BRY5382

NEMA® is a registered trademark of the National Electrical Manufacturers Association.



Product Dimensions

Inches (mm)

A	4.06" (103.1)
B	3.28" (83.3)
C	1.54" (39.1)
D	1.16" (29.5)

