

Hospital Grade Devices



Surge Suppression Receptacles



- Damage-alert alarm sounds when surge protection is no longer functioning, muting screw allows damage-alert alarm to be silenced until device is replaced
- Power-on indicator light verifies that suppression circuit is fully functional, light off means power has been interrupted, flashing light indicates surge protection circuitry has been damaged
- Automatic grounding clip
- High-impact nylon face resists breakage
- Distinctive surge symbol provides quick visual identification of surge suppression receptacle

Hospital Grade • Standard and Isolated Ground Surge Suppression Receptacles




		Surge Suppression Receptacles with Light and Alarm, 240 Joules/15,000 Amps per Mode	
Face		Nylon Face	
		Hospital Grade	
Rating	Color	Standard	with Isolated Ground
NEMA 5-15, 15A 125V 	Blue	SP82A	SP82IGA
	Gray	SP82GYA	SP82IGGYA
	Ivory	SP82IA	SP82IGIA
	Orange	—	SP82IGOA
	Red	—	SP82IGRA
	White	SP82WA	SP82IGWA
NEMA 5-20, 20A 125V 	Blue	SP83A	SP83IGA
	Gray	SP83GYA	SP83IGGYA
	Ivory	SP83IA	SP83IGIA
	Orange	—	SP83IGOA
	Red	—	SP83IGRA
	White	SP83WA	SP83IGWA

Product Dimensions Inches (mm)

Receptacle	
A	4.04" (102.6)
B	2.80" (71.1)
C	1.72" (43.7)
D	1.60" (40.6)
E	1.24" (31.5)

Note: See page A-5 for dimensions on adapter plates and portable boxes.



Lexan® is a registered trademark of Sabic Innovative Plastics.