

Locking Devices

Power Interrupting Accessories

20A Power Interrupting Accessories Inches (mm)



Single Gang 1.40" (35.6) Opening			Receptacle Plates, Cast Aluminum		"Mini" Weather Protective Boots	
Stainless Steel, Type 302/304	Brass	Black Nylon	With Lift Cover, Indoor Use Box Mount	Weather Protective with Cover F.S. Box Mount	Female Connector	Male Plug
SS7	SB7	P7BK	23007	7418B	20424**	20425**

30A Power Interrupting Accessories



Liquid-Tight Metallic Conduit Adapters for Use with Plugs and Connectors		Receptacle Plates, Cast Aluminum		"Mini" Weather Protective Boots	
With 1/2 in. conduit	With 3/4 in. conduit	Weather Protective Plate for Wet Locations with Cover Closed	No Lift Cover	Female Connector	Male Plug
SAB12A*	SAB34A*	20405	20406	20424**	20425**

Note: *Not CSA Certified.

**Boots are not UL Listed or CSA Certified.

Boots are not available for 5-wire 30 amp power interrupting plugs and connectors.

Product Dimensions Inches (mm)

	Receptacle Plates		
	Cover	No Cover	Box
A	4.56" (115.8)	4.56" (115.8)	4.59" (116.5)
B	3.25" (82.6)	3.25" (82.6)	3.87" (98.2)
C	2.84" (72.1)	2.84" (72.1)	2.71" (68.8)
D	1.88" (47.8)	1.88" (47.8)	1.31" (33.3)
E	1.16" (29.5)	0.59" (15.0)	1 1/2" NPT TAP
F	0.38" (9.7)	0.38" (9.7)	—

