









15A and 20A Straight Blade Plugs, Connectors and Receptacles Inches (mm)

UL Type 4, 4X, 6P

IP65, 66, 67, 69k*

SUITABILITY



Rating Plug	Rating Connector	Poles/ Wires	Cord Diameter	Color	Thermoplastic Elastomer			
					Plug	Connector	Receptacle with Lift Cover	Duplex Recept. with Lift Cover
NEMA 5-15, 15A 125V 	 2-Pole 3-Wire	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow Black Clear	BRY14W47 BRY14W47BK BRY14W47WC	BRY15W47 BRY15W47BK BRY15W47WC	BRY60W47 BRY60W47BK —	BRY60W47D —
NEMA 6-15, 15A 250V 	 2-Pole 3-Wire	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow	BRY14W49	BRY15W49	BRY60W49	BRY60W49D
NEMA 5-20, 20A 125V 	 2-Pole 3-Wire	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow	BRY14W33 BRY14W33WC	BRY15W33 BRY15W33WC	BRY60W33 —	BRY60W33D —
NEMA 6-20, 20A 250V 	 2-Pole 3-Wire	2-Pole 3-Wire	.325"-.625" (8.3-15.9)	Yellow	BRY14W48	BRY15W48	BRY60W48	BRY60W48D

Note: *Single and duplex receptacles while in use, not with cover closed.
Black devices are available, consult factory.

Product Dimensions Inches (mm)

15A and 20A Straight Blade	
Plugs	A 1.85" (47.07)
	B 3.16" (80.27)
Connectors	C 1.85" (47.07)
	D 4.42" (112.14)

15A and 20A Straight Blade Receptacles	
A	4.56" (115.9)
B	3.10" (78.7)
C	1.20" (30.6)
D	3.25" (82.6)
E	1.88" (47.6)
F	1.26" (32.0)
G	1.63" (41.4)
H	5.00" (127.0)

