

Temporary Lighting

Construction Site Lighting



Bryant's outdoor approved construction site lighting line includes both heavy-duty metal halide lights and light strings for working in rugged environments. The metal halide fixtures feature extremely strong and compact heads with bulbs rated to last 10,000 hours. All frames are powder-coated yellow for safety and are constructed of a durable 1.25 inch, 12 gauge steel tube.

Light strings for all applications are available in a variety of models as well as a choice of metal or plastic guards. Light sockets are spaced 10 feet apart and all sockets, plugs, and connectors are molded for added durability. In addition, the highly impact-resistant material makes for easy transportation and storage when not in use. Bulbs can be incandescent, fluorescent or LED. Consider choosing LED lighting for a durable bulb that saves energy, provides instant illumination and are rated to last 50,000 hours.



BRYMHHB400

Metal Halide and LED Lights

Description	Rating	Watts	Lumen Output	Cord Length	Catalog Number
High bay metal halide light with wire guard.	15A 125V	400	29,000	3 ft.	BRYMHHB400
High bay LED light with wire guard.	15A 125V	120	14,000	5 ft.	BRYLEDHB120
	15A 125V	100	12,000	5 ft.	BRYLEDHB100
	15A 125V	60	7,200	5 ft.	BRYLEDHB60



BRYLEDHB120

LED Stringer Lights

Description	No. of Fixtures	Rating	Cord Type	Lumen Output	Cord Length	Catalog Number
90 LEDs per fixture, light string with magnetic base included.	1	15A 125V	#18/2 SJTW	450*	20 ft.	BRY182S20LED
90 LEDs per fixture, light string.	5	15A 125V	#18/2 SJTW	450*	50 ft.	BRY182S50LED
	10	15A 125V	#18/2 SJTW	450*	100 ft.	BRY182S100LED
Magnetic clip bracket for LED light string.						BRYSTMC

Note: *Lumens per fixture.



BRY182S50LEDH

A Type (Edison) Locking and Straight Blade Light Strings

Description	Max Watts**	Rating	Cord Type	Fixtures	Cord Length	Catalog Number
Locking light string; plastic guards.	150	20A 125V	#12/3 STJW	10	100 ft.	BRY123SJ100PT
Straight Blade light string; plastic guards.	150	15A 125V	#14/2 STJW	10	100 ft.	BRY142SJ100PS
	150	15A 125V	#12/3 STW	10	100 ft.	BRY123S100PS
	150	15A 125V	#12/3 STJW	10	100 ft.	BRY123SJ100PS
Straight Blade light string; metal guards.	150	15A 125V	#12/3 STW	10	100 ft.	BRY123S100MS
Straight Blade light string; plastic guards.	150	15A 125V	#12/3 STW	5	50 ft.	BRY123S50PS
Straight Blade light string; metal guards.	150	15A 125V	#12/3 STW	5	50 ft.	BRY123S50MS
Replacement plastic guard for temporary light strings.						BRYSTPG
Replacement heavy duty metal guard for temporary light strings.						BRYSTMG

Note: **Max watts per fixture. The total wattage must be considered when daisy chaining lights strings to each other.



BRY142SJ100PS



BRYSTMC



BRYSTPG



BRYSTMG