

# Temporary Lighting

## Construction Site Lighting



Bryant's outdoor approved construction site lighting line includes both heavy-duty metal halide lights and light strings for working in rugged environments. The metal halide fixtures feature extremely strong and compact heads with bulbs rated to last 10,000 hours. All frames are powder-coated yellow for safety and are constructed of a durable 1.25 inch, 12 gauge steel tube.

Light strings for all applications are available in a variety of models as well as a choice of metal or plastic guards. Light sockets are spaced 10 feet apart and all sockets, plugs, and connectors are molded for added durability. In addition, the highly impact-resistant material makes for easy transportation and storage when not in use. Bulbs can be incandescent, fluorescent or LED. Consider choosing LED lighting for a durable bulb that saves energy, provides instant illumination and are rated to last 50,000 hours.

### Metal Halide Lights

Description	Rating	Watts	Lumen Output	Cord Length	Catalog Number
5 -10 ft. metal halide cart light with portable detachable ballast	15A 125V	1,000	110,000	—	<b>BRYMH1000</b>
6 -12 ft. metal halide cart light	15A 125V	2,000	220,000	—	<b>BRYMH2000</b>
High bay metal halide light with wire guard	15A 125V	400	29,000	3 ft.	<b>BRYMHHB400</b>



**BRYMH1000**



**BRYMHHB400**

### LED Stringer Lights

Description	No. of Fixtures	Rating	Cord Type	Lumen Output	Cord Length	Catalog Number
90 LEDs per fixture, light string with magnetic base included	1	15A 125V	18/2 SJTW	450*	20 ft.	<b>BRY182S20LED</b>
90 LEDs per fixture, light string	5	15A 125V	18/2 SJTW	450*	50 ft.	<b>BRY182S50LED</b>
	10	15A 125V	18/2 SJTW	450*	100 ft.	<b>BRY182S100LED</b>
28W High power LED light string with in line ON/OFF switch	—	15A 125V	16 AWG SJTOW	2,928	6 ft.	<b>BRYLS2834</b>
Magnetic clip bracket for LED lights switch, single fixture	—	—	—	—	—	<b>BRYSTM C</b>

Note: \*Lumens per fixture.

### A Type (Edison) Locking and Straight Blade Light Strings

Description	Max Watts*	Rating	Cord Type	Fixtures	Cord Length	Catalog Number
Locking light string, plastic guards	150	20A 125V	12/3 STW	10	100 ft.	<b>BRY123S100PT</b>
	150	20A 125V	12/3 STJW	10	100 ft.	<b>BRY123SJ100PT</b>
Locking light string, metal guards	150	20A 125V	12/3 STW	10	100 ft.	<b>BRY123S100MT</b>
Straight blade light string, plastic guards	150	15A 125V	14/2 STJW	10	100 ft.	<b>BRY142SJ100PS</b>
	150	15A 125V	12/3 STW	10	100 ft.	<b>BRY123S100PS</b>
	150	15A 125V	12/3 STJW	10	100 ft.	<b>BRY123SJ100PS</b>
Straight blade light string, metal guards	150	15A 125V	12/3 STW	10	100 ft.	<b>BRY123S100MS</b>
Straight blade light string, plastic guards	150	15A 125V	12/3 STW	5	50 ft.	<b>BRY123S50PS</b>
Straight blade light string, metal guards	150	15A 125V	12/3 STW	5	50 ft.	<b>BRY123S50MS</b>
Replacement plastic guard for temporary light strings	—	—	—	—	—	<b>BRYSTPG</b>
Replacement heavy duty metal guard for temporary light strings	—	—	—	—	—	<b>BRYSTM G</b>

Note: \*Max watts per fixture.

### Fluorescent Light Strings

Description	Wattage	Rating	Cord Type	Lumen Output	Cord Length	Catalog Number
Fluorescent light string, 34.5 in. single fixture with hanging straps	50	15A 125V	16 AWG SJTOW	3,750	6 ft.	<b>BRYFS5035</b>
Fluorescent light string, 48.5 in. single fixture with hanging straps	25	15A 125V	16 AWG SJTOW	2,125	6 ft.	<b>BRYFS2549</b>



**BRYFS2549**  
Straps not Shown