



Field Termination solutions for direct attach Modular Plug Terminated Links (MPTL).

### Specifications

- Cable supported: F/FTP, S/FTP, F/UTP and UTP Cable jacket O.D. 0.236–0.315" (6–8mm)
- Conductor: Solid: 22–26AWG
- Performance: ANSI/TIA-568-C.2 Category 6A and Category 6 channel
- Full 802.3bt (4PPoE) support, Type 3 and 4
- UL Plenum rated

## NEXTSPEED® COBRA-LOCK™ Field Termination Plugs

| Description   | Catalog No. |
|---|-------------|
| CAT6A Field Termination MPTL Plug                     | SP6A        |
| CAT6 Field Termination MPTL Plug                      | SP6         |
| CAT6A Field Termination MPTL Plug with 90° Cable Exit | SP6A90      |
| CAT6 Field Termination MPTL Plug with 90° Cable Exit  | SP690       |



## NEXTSPEED COBRA-LOCK 6A Coupler

| Description                                    | Catalog No. |
|--|-------------|
| CAT6A MPTL Coupler                             | SC6A        |
| CAT6A MPTL 18" Pre-Terminated Coupler Assembly | SCP6A       |

Note: See page D08 for additional MPTL Assembly color and length options.



## Jack Accessories

### Jack Dust Covers, Compatible with the HXJ Xcelerator Jacks Only

| Description                   | Catalog No. |
|-------------------------------|-------------|
| Polypropylene, clear, 25-pack | HXJDC25     |

Note: Mounts within the icon slots located above the RJ45 opening. Cannot be used with SJ shielded jack series.



### Secure-IT RJ-45 Port Blocker

Physically lock out access to individual RJ-45 ports with the Secure-IT Port Blocker. Compatible with any RJ-45 port, the blocker inserts easily and requires the supplied tool to remove.

| Description                | Catalog No. |
|----------------------------|-------------|
| Locking RJ-45 port blocker | RJ45PB50    |

Note: Fits any RJ-45 port.

Note: See color chart on page B02.



### Jack Icons, Compatible with the HXJ Xcelerator Jacks Only

100-pack, snaps onto jack nose

| Color  | Blank Catalog No. | Computer Catalog No. | Telephone Catalog No. |
|--------|-------------------|----------------------|-----------------------|
| Black  | IBK100            | IBK100C              | IBK100T               |
| Blue   | IB100             | IB100C               | IB100T                |
| Brown  | IBN100            | IBN100C              | IBN100T               |
| Gray   | IGY100            | IGY100C              | IGY100T               |
| Green  | IGN100            | IGN100C              | IGN100T               |
| Ivory  | IEI100            | IEI100C              | IEI100T               |
| Orange | IOR100            | IOR100C              | IOR100T               |
| Purple | IP100             | IP100C               | IP100T                |
| Red    | IR100             | IR100C               | IR100T                |
| White  | IW100             | IW100C               | IW100T                |
| Yellow | IY100             | IY100C               | IY100T                |

Note: Cannot be used with SJ shielded jack series; custom icon numbering and labeling available; contact Customer Service for details.