



## Specifications

- Overall jacket O.D.: 0.215" (Plenum); 0.225" (Riser)
- Conductor: 23 AWG solid bare copper
- Sweep tested to 550 MHz
- 5dB headroom above Cat6 standards: NEXT, PSNEXT, ACRF, PSACRF

## Standards

- ANSI/TIA 568.2-D and ISO/IEC 11801 Class E Category 6 Cabling
- 10BASE-T through 1000BASE-T, 10GBASE-T per TSB-155
- IEEE 802.3af (PoE), IEEE 802.3at (PoE+), IEEE 802.3bt (4PPoE Type 3 and 4)
- UL Listed

## NEXTSPEED® Category 6 UTP Cable

**NVP: Plenum 70%, Riser 68%**

Color	Plenum REELEX® Box	Riser REELEX® Box
Black	HC6RPBK	HC6RRBK
Blue	HC6RPB	HC6RRB
Gray	HC6RPGY	HC6RRGY
Green	HC6RPGN	HC6RRGN
Orange	HC6RPOR	HC6RROR
Pink	HC6RPPK	HC6RRPK
Purple	HC6RPP	HC6RRP
Red	HC6RPR	HC6RRR
White	HC6RPW	HC6RRW
Yellow	HC6RPY	HC6RRY



## Specifications

- Overall jacket O.D.: 0.19 (Plenum); 0.20 (Riser)
- Conductor: 23 AWG solid bare copper
- Sweep tested to 500 MHz
- Guaranteed Category 6 performance

## Standards

- ANSI/TIA 568.2-D and ISO/IEC 11801 Class E Category 6 Cabling
- 10BASE-T through 1000BASE-T
- IEEE 802.3af (PoE), IEEE 802.3at (PoE+), IEEE 802.3bt (4PPoE Type 3 and 4)
- UL Listed

## NEXTSPEED® Link 6 UTP Cable

**4-pair; NVP: Plenum 73%, Riser 70%**

Color	Plenum REELEX® Box	Riser REELEX® Box
Black	HC6RPEBK	HC6RREBK
Blue	HC6RPEB	HC6RREB
Gray	HC6RPEGY	HC6RREGY
Green	HC6RPEGN	HC6RREGN
Orange	HC6RPEOR	HC6RREOR
Pink	HC6RPEPK	HC6RREPK
Purple	HC6RPEP	HC6RREP
Red	HC6RPER	HC6RRER
White	HC6RPEW	HC6RREW
Yellow	HC6RPEY	HC6RREY



Note: Additional packaging options available. Please contact Customer Service or your local Hubbell Territory Manager for more information. REELEX is licensed and patented by Windings Inc.