



### Specifications

- Outer jacket nominal O.D.: 0.28" (Plenum), 0.29" (Riser)
- Conductor: 23 AWG solid bare copper
- Polyester backed aluminum foil shield
- Application: third party qualified for 10 Gigabit Ethernet transmission IEEE 802.3an
- Qualified for PoE IEEE 802.3bt

### Standards

- UL Verified TIA 568.2-D Category 6A cable
- ISO 11801 Class E<sub>A</sub> Category 6A cable
- UL Listed

## NEXTSPEED® Ascent Category 6A FTP Cable

NVP: Plenum 70%, Riser 68%

Color	Plenum Spool	Riser Spool
Blue	<b>C6AFTPSPB</b>	<b>C6AFTPSPRB</b>
Gray	<b>C6AFTPSPGY</b>	<b>C6AFTPSPRGY</b>
Green	<b>C6AFTPSPGN</b>	<b>C6AFTPSPRGN</b>
White	<b>C6AFTPSPW</b>	<b>C6AFTPSPRW</b>
Yellow	<b>C6AFTPSPY</b>	<b>C6AFTPSPRY</b>



Note: Other colors available upon request.



### Specifications

- Outer jacket nominal O.D.: 0.28 (Plenum); 0.29 (Riser)
- Conductor: 23 AWG solid bare copper
- Polyester backed aluminum foil shield

### Standards

- TIA 568.2-D Category 6 cable
- ISO 11801 Class E Category 6 cable
- UL Listed

## NEXTSPEED® Ascent Category 6 F/UTP Cable

NVP: Plenum 70%, Riser 68%

Color	Plenum Spool	Riser Spool
Blue	<b>C6FTPSPB</b>	<b>C6FTPSPRB</b>
Gray	<b>C6FTPSPGY</b>	<b>C6FTPSPRGY</b>
Green	<b>C6FTPSPBK</b>	<b>C6FTPSPRGN</b>
White	<b>C6FTPSPW</b>	<b>C6FTPSPRW</b>
Yellow	<b>C6FTPSPY</b>	<b>C6FTPSPRY</b>



Note: Other colors available upon request.