



**Specifications**

- Rugged polyolefin outer jacket; nominal O.D.: 0.36"
- Conductor: 23 AWG solid bare copper
- SAP impregnated aramid yarns
- F/UTP construction: polyester backed aluminum foil shield
- Polyolefin inner jacket
- Non-conductive, water-blocking gel
- Increased operating temperature range: -40C to 70 °C (-40F to 158F)

**Standards**

- TIA 568.2-D Category 6A Cable

**NEXTSPEED® Category 6A OSP Outdoor Cable**

**NVP: 67%**

**Color**  
Black

**Spool**  
**C6ASOPBK**



**Specifications**

- Rugged polyolefin outer jacket; nominal O.D.: 0.25"
- Conductor: 24 AWG solid bare copper
- Non-conductive, water-blocking gel
- UTP construction
- Increased operating temperature range: -40C to 70 °C (-40F to 158F)

**Standards**

- TIA 568.2-D Category 6 Cable

**NEXTSPEED® Category 6 OSP Outdoor Cable**

**NVP: 63%**

**Color**  
Black

**Spool**  
**C6SOPBK**

