



①



③



④



⑤



⑥

## Specifications

- Punch down 110 style termination
- Connectors: HDMI 19-pin, Type A, female connector, gold plated 2μ"
- IDC Contact: phosphor bronze with tin plating over nickel under plating
- Material: powder coated cold rolled steel and high-impact thermoplastic

## 4K UHD HDBaseT™ Frames and Modules

4K HDMI, USB, 3.5mm audio, IR extender, black, single 4-pair, CAT6A, UTP cable installation, up to 328ft (100m); 5V DC Power Supply required on each end (sold separately)

Description	Catalog No.
Kit	① ISFHD5BK
Transmitter	ISFHDT5BK
Receiver	ISFHDR5BK

## HDBaseT™ AV Switching Transmitters

Auto-switching AV HDBaseT transmitters with USB, IR, black, single 4-pair UTP cable installation; combine with ISFHDR5BK to complete system; 5V DC power supply required on each end (sold separately)

Description	Catalog No.
(1) VGA, (1)HDMI Transmitter	③ ISFHDT421BK
(3) HDMI Transmitter	ISFHDT431BK

## Tamper-Resistant Receptacle with 5V DC Output

Description	Color	Catalog No.
USB charger	Black	AVPS152BK
TR receptacle,	Ivory	AVPS152I
(1) USB port 5A,	Gray	AVPS152GY
5V DC output,	Office White	AVPS152LA
15A, 125V AC	White	⑤ AVPS152W
decorator duplex		

## HDMI Patch Cords

24AWG, black, non-plenum

Description	Catalog No.
3 foot	⑥ HCH03BK
6 foot	HCH06BK
10 foot	HCH10BK

## USB 2.0 High Speed 110 Extenders, 100ft

Description	Color	1.5 Unit Module
4-pair UTP cable installation, 5V DC up to 100ft (305m)	Black	IMU11015BK
	Ivory	IMU11015EI
	Gray	IMU11015GY
	Office White	④ IMU11015OW
	White	IMU11015W

Note: Includes send and receive pair and 5V DC power supply.

## External 5V DC Power Supply

Catalog No.	HDMIDC5V2
-------------	-----------

## Infrared Emitter and Receiver Kit

Catalog No.	AVIR
-------------	------

## AV Panel

Flat, 2U, (8) single gang decorator openings, horizontal mount, black	HPD8
---	------

HDBaseT is a trademark of the HDBaseT Alliance. See color chart on page F02. Modules and frames are featured on pages F05-F07.