

**Standard MPO 12-Port LC Duplex Cassettes**

Type A polarity (straight through, pin 1 to pin 1) MPO input: (1) MPO male pinned receptacle



|                      |                 |                   |                |               |               |               |
|----------------------|-----------------|-------------------|----------------|---------------|---------------|---------------|
| <b>Fiber Type</b>    | OM4             | OM4               | OM3            | OM2           | OM1           | OS2           |
| <b>Adapter Color</b> | Aqua            | Violet            | Aqua           | Black         | Beige         | Blue          |
| <b>Catalog No.</b>   | <b>OCLC50G4</b> | <b>OCLC50G4VI</b> | <b>OCLC50G</b> | <b>OCLC50</b> | <b>OCLC62</b> | <b>OCLCSM</b> |

**Standard MPO 24-Port LC Duplex Cassettes**

Type A polarity (straight through, pin 1 to pin 1) MPO input: (2) MPO male pinned receptacles



|                      |                  |                    |                 |                |                |                |
|----------------------|------------------|--------------------|-----------------|----------------|----------------|----------------|
| <b>Fiber Type</b>    | OM4              | OM4                | OM3             | OM2            | OM1            | OS2            |
| <b>Adapter Color</b> | Aqua             | Violet             | Aqua            | Black          | Beige          | Blue           |
| <b>Catalog No.</b>   | <b>OCLCD50G4</b> | <b>OCLCD50G4VI</b> | <b>OCLCD50G</b> | <b>OCLCD50</b> | <b>OCLCD62</b> | <b>OCLCDSM</b> |

**Standard MPO 24-Port LC Quad Cassettes**

Type A polarity (straight through, pin 1 to pin 1) MPO input: (2) MPO male pinned receptacles



|                      |                  |                    |                 |                |                |                |
|----------------------|------------------|--------------------|-----------------|----------------|----------------|----------------|
| <b>Fiber Type</b>    | OM4              | OM4                | OM3             | OM2            | OM1            | OS2            |
| <b>Adapter Color</b> | Aqua             | Violet             | Aqua            | Black          | Beige          | Blue           |
| <b>Catalog No.</b>   | <b>OCLCQ50G4</b> | <b>OCLCQ50G4VI</b> | <b>OCLCQ50G</b> | <b>OCLCQ50</b> | <b>OCLCQ62</b> | <b>OCLCQSM</b> |

Note: See color chart on page G02.