



Specifications

- Black powder coated
- Slide-out tilt-down bottom tray for maximum access
- Two removable top covers
- Optional front / rear lockable doors
- Expanded cable and splice tray storage
- User-friendly port assignment label attached to front door
- Keyed screw holes on mounting brackets, for ease of installation

Standards

- EIA/ECA-310-E
- TIA-569-D50



①



②



③

Enhanced Rack Mount Enclosures

Rack Units	Height In (mm)	Width In (mm)	Depth In (mm)	FSP Panel Capacity	Splice Tray Capacity	Max LC Port Capacity	Standard Catalog No.
1	1.75" (44)	19" (483)	17" (432)	3	3	72	FCR1U3SPX
2	3.5" (89)	19" (483)	17" (432)	6	6	144	① FCR2U6SPX
2	3.5" (89)	19" (483)	17" (432)	9	6	216	FCR2U9SPX
3	5.25" (133)	19" (483)	17" (432)	12	12	288	② FCR3U12SPX
4	7.00" (178)	19" (483)	17" (432)	15	16	360	FCR4U15SPX

Note: Locking option requires FLOCKx Kits. FCR2U9SPX does not accept Plug-n-Play OC Series cassettes.

Enhanced Rack Mount Enclosure, Vertical Panel Mounting

Rack Units	Height In (mm)	Width In (mm)	Depth In (mm)	FSP Panel Capacity	Splice Tray Capacity	Max LC Port Capacity	Standard Catalog No.
4	7.00" (178)	19" (483)	17" (432)	12	16	288	③ FCR4U12SPVX

Accessories

Description	Catalog No.
Cable management kit, bend radius clip, 4-pack	FBRMGTCCLK4
Splice tray, 12 fusion splice	⑥ STRAY12F
Splice tray, 24 fusion splice	STRAY24F
User's side (front) lock kit	FLOCK1
Technician's side (rear) lock kit	FLOCK2



⑥