



## Specifications

- Mounts to wall; equipment positioned vertically
- Weight rating: 50lb.
- Material: cold rolled steel
- Finish: black powder coated

## Wall Mount Brackets

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Hole Type	Catalog No.
2	4.55" (116)	19.25" (489)	3.9" (99)	12-24 threaded	<b>WB2</b>
4	8.05" (204)	19.25" (489)	7.4" (188)	12-24 threaded	<b>WB4</b>
6	8.05" (204)	19.25" (489)	11.15" (283)	12-24 threaded	<b>WB6</b>



## Specifications

- Mounts to wall or ladder tray; panels positioned at a 45 degree angle
- Weight rating: 25lb.
- Material: CRS
- Finish: black powder coated

## Wall or Tray Mount Brackets

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Hole Type	Catalog No.
2	5" (127)	20" (508)	6.45" (164)	12-24 threaded	<b>TBA2</b>
3	6.39" (162)	20" (508)	6.45" (164)	12-24 threaded	<b>TBA3</b>
4	7.68" (195)	20" (508)	8.18" (208)	12-24 threaded	<b>TBA4</b>



## Specifications

- Mounts to ladder tray; underneath or off stringer
- Weight rating: 25lb.
- Material: CRS
- Finish: black powder coated

## Tray Mount Brackets

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Hole Type	Catalog No.
2	5" (127)	23.5" (597)	3" (76.2)	12-24 threaded	<b>TBS2</b>
4	8.5" (216)	23.5" (597)	3" (76.2)	12-24 threaded	<b>TBS4</b>
6	12" (305)	23.5" (597)	3" (76.2)	12-24 threaded	<b>TBS6</b>