



## Equipment Shelves

Stationary shelf, 16 gauge, 12-24 mounting hardware

Type	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Load (lb)	Shelf	Catalog No.
Cantilevered	3.5" (89)	19" (483)	14" (356)	50	Solid	① <b>MCCCS19</b>
					Perforated	<b>MCCCS19P</b>
Cantilevered	3.5" (89)	19" (483)	11" (279)	50	Perforated	<b>HSC11P</b>
Cantilevered	7" (178)	19" (483)	20" (508)	200	Solid	② <b>MCCCWS19HD</b>
Center-weighted	3.5" (89)	19" (483)	19" (483)	75	Solid	③ <b>MCCCWS19</b>

## Waterfall Top for 3" and 6" Deep Relay Racks

### Description

Black, 2 Piece cable drop radius for top of 3" and 6" Deep Relay Racks

### Catalog No.

**HRRCR**



## 19" Filler Panels

Black, includes (1) panel and (4) 12-24 screws

Rack Units	Height Inches (mm)	Flat Catalog No.	Angled Catalog No.
1	1.75" (44)	<b>MCCBP175</b>	<b>ABP175</b>
2	3.50" (89)	<b>MCCBP350</b>	<b>ABP350</b>
4	7.00" (178)	<b>MCCBP700</b>	-



## Relay Rack Isolation Pads

Polyester fiberglass pad for isolating relay racks from cement floor, includes (4) isolating bushings for bolts and (4) cement anchors

Type	Use With	Catalog No.
1-piece	HPWxxRR19	<b>HRRP3</b>
2-piece	HPW84RR19D, SF8419xx	<b>HRRP</b>
2-piece	HHRxxx, HPW84RR23	<b>HRRPW</b>



## Cement Anchoring Bolts

Galvanized anchor bolts for securing relay racks to cement floor

Length Inches (mm)	Diameter Inches (mm)	Qty	Catalog No.
3.75" (89)	3/8"	4	<b>HPWRA</b>



## Extender Brackets, 23"

Black, includes (2) brackets and (1) mounting hardware kit, converts 23" rack mount space to 19"

Length Inches (mm)	Catalog No.
23" (584)	<b>BREXTB235</b>

