


M Series without covers

Specifications

- 14 gauge cold rolled steel
- 0.225" steel rod diameter supports
- Black powder coated


Installation

- Cable radius pass-through holes
- Hinged cover can be removed
- For flush mount, use HMx7x with VM vertical cable managers



Side View

①



Side View

②



Front

③



④

Horizontal Cable Management

Height (RU)	Front Extension	Rear Extension	Cover	Catalog No.
1	7" (178)	-	Included	① HM17C
2	7" (178)	-	Included	HM27C
3	7" (178)	-	Included	HM37C
4	7" (178)	-	Included	HM47C
1	7" (178)	7" (178)	Included	③ HM177C
2	7" (178)	7" (178)	Included	HM277C
3	7" (178)	7" (178)	Included	HM377C
4	7" (178)	7" (178)	Included	HM477C
1	4" (102)	-	Included	② HM14C
2	4" (102)	-	Included	HM24C
3	4" (102)	-	Included	HM34C
4	4" (102)	-	Included	HM44C
1	4" (102)	-	-	HM14
2	4" (102)	-	-	HM24
3	4" (102)	-	-	HM34
1	2" (51)	-	Included	HM12C
2	2" (51)	-	Included	HM22C

Cable Management Spools

Color	Description Inches (mm)	Qty	Catalog No.
Black	3" (76)	50	④ ICKSS
	6" (152)	50	ICKSS6
	9" (229)	50	ICKSS9

Horizontal Cover Only

Height (RU)	Catalog No.
1	HM1C
2	HM2C
3	HM3C
4	HM4C