



S Series without covers

Specifications

- 14 gauge cold rolled steel
- Hinged or lift-off cover
- Black powder coated

Installation

- Pass-through holes for cables
- Covers lift off



①



②



③

Horizontal Cable Management

| Height (RU) | Front Extension Inches (mm) | Rear Extension Inches (mm) | Cover | Catalog No. |
|-------------|-----------------------------|----------------------------|----------|----------------|
| 1 | 6" (152) | - | Included | HS16C |
| 2 | 6" (152) | - | Included | HS26C |
| 1 | 3" (76) | 6" (152) | Included | HS136C |
| 2 | 3" (76) | 6" (152) | Included | HS236C |
| 1 | 3" (76) | - | Included | ① HS13C |
| 2 | 3" (76) | - | Included | HS23C |
| 1 | 3" (76) | - | - | HS13 |
| 2 | 3" (76) | - | - | ② HS23 |

Horizontal Cover Only

| Height (RU) | Catalog No. |
|-------------|-------------|
| 1 | HS1C |
| 2 | HS2C |

Vertical Covers

38.5" height

| Width Inches (mm) | Qty | Catalog No. |
|-------------------|-----|---------------|
| 3" (76) | 1 | ③ VSC3 |
| 4" (102) | 1 | VSC4 |
| 6" (152) | 1 | VSC6 |

Gates

| Width Inches (mm) | Qty | Catalog No. |
|-------------------|-----|-------------|
| 4" (102) | 16 | VCG4 |
| 6" (152) | 16 | VCG6 |

Accessories

| Description | Qty | Catalog No. |
|----------------|-----|-----------------|
| 3" spools | 50 | ④ ICKSS* |
| VS joining kit | 1 | VCJK |
| VS hinge kit | 2 | ⑤ VCKH |

Note: *Add 6 for 6", add 9 for 9"; see page L04.