

NEXTFRAME | Wire Basket Tray, Stainless Steel Round Cross-Wire



Features

- Type 304L and 316S stainless steel
- Meets ASTM A580 specifications
- 4.5mm round wire minimum
- Stainless splice kits and ceiling supports are available

Applications

- Food processing
- Wash down areas
- Corrosive environments
- Outdoor installations
- Marine

Stainless Steel Round Cross-Wire

10 Feet per Length
118.3" (3m)
10 Piece Min. Order Qty.

2" Deep Tray




Tray Width	Load (lb/ft)	Tray Weight per Length (lb)	Splice Quantity		Round	
			90° Sweep Elbow	Straight Splice	Type 304L	Type 316S
4" (102)	45	7	2	2	HBT0204S04	HBT0204S16
6" (152)	50	9	3	4	HBT0206S04	HBT0206S16
8" (203)	52	10.5	4	4	HBT0208S04	HBT0208S16
12" (305)	58	12	6	4	HBT0212S04	HBT0212S16
16" (406)	70	15	7	4	HBT0216S04	HBT0216S16
18" (457)	70	23	9	4	HBT0218S04	HBT0218S16
20" (508)	73	25	9	5	HBT0220S04	HBT0220S16
22" (559)	73	27	12	5	HBT0222S04	HBT0222S16
24" (610)	75	31	12	5	HBT0224S04	HBT0224S16
26" (660)	73	33	13	6	HBT0226S04	HBT0226S16
28" (711)	73	35	14	6	HBT0228S04	HBT0228S16
30" (762)	70	38	15	6	HBT0230S04	HBT0230S16
32" (813)	70	39	16	6	HBT0232S04	HBT0232S16

4" Deep Tray



4" (102)	49	12	2	4	HBT0404S04	HBT0404S16
6" (152)	49	13	3	5	HBT0406S04	HBT0406S16
8" (203)	78	15	4	6	HBT0408S04	HBT0408S16
12" (305)	78	23	6	6	HBT0412S04	HBT0412S16
16" (406)	108	27	7	7	HBT0416S04	HBT0416S16
18" (457)	116	29	9	7	HBT0418S04	HBT0418S16
20" (508)	116	31	9	7	HBT0420S04	HBT0420S16
22" (559)	116	33	12	8	HBT0422S04	HBT0422S16
24" (610)	116	35	12	8	HBT0424S04	HBT0424S16
28" (711)	108	39	14	9	HBT0428S04	HBT0428S16

6" Deep Tray



8" (203)	116	23	4	6	HBT0608S04	HBT0608S16
12" (305)	123	27	6	6	HBT0612S04	HBT0612S16
16" (406)	123	31	7	7	HBT0616S04	HBT0616S16
18" (457)	127	33	9	7	HBT0618S04	HBT0618S16
20" (508)	127	35	9	7	HBT0620S04	HBT0620S16
22" (559)	127	37	12	8	HBT0622S04	HBT0622S16
24" (610)	150	39	12	8	HBT0624S04	HBT0624S16

8" Deep Tray



8" (203)	116	27	4	8	HBT0808S04	HBT0808S16
12" (305)	116	31	6	8	HBT0812S04	HBT0812S16
16" (406)	116	35	7	9	HBT0816S04	HBT0816S16
18" (457)	116	37	9	9	HBT0818S04	HBT0818S16
20" (508)	116	39	9	9	HBT0820S04	HBT0820S16

Note: All dimensions are +/- 0.25".