



Specifications

- 300 lb. load capacity
- UL 2416 listed
- Ground provisions per TIA-607
- Adjustable depth mounting rails with threaded #12-24 holes
- Installed grounding jumpers to bond all cabinet sections
- Reversible cabinet, for left- or right-hand door swing
- Fan knockouts, for easy installation of optional fans
- Rectangular knockout, to retrofit pre-installed cable
- Tinted plexiglass door standard
- Front door and center sections keyed alike
- Rear panel mounting holes spaced for 16" on center studs
- Accommodates FCR-X rack-mount fiber enclosure
- Base panel with "belt loops", to mount Hubbell bracket kits

HQC QUADCAB® Wall Mount Cabinets

Includes: cabinet, (1) pair 19" mounting rails, (2) CH751 locks and keys, installed bonding conductors, powder-coated, black

Rack Unit (RU)	Rear Wall Unit (RWU)*	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	DoorStyle	Catalog No.
12	2	24" (610)	22.6" (574)	24" (610)	Plexi Window	HQC2424
				32" (813)		HQC2432
19	4	36" (914)	22.6" (574)	24" (610)	Plexi Window	HQC3624
				32" (813)		HQC3632
26	6	48" (1219)	22.6" (574)	24" (610)	Plexi Window	HQC4824
				32" (813)		HQC4832



Note: *Rear Wall Unit (RWU) is the total number of rack unit space that can be mounted to rear wall lances of cabinet, via bracket accessories.

Accessories

Product Number	Description
HQCCK	HQC Caster Kit with 5 stem wheels and nuts
HQCFK	HQC Fan Kit, one (1), 75 CFM Fan, hardware
HQCFF	HQC Fan Filter Kit w/Filter Housing, Fan Guard, Filter
HQCFFR5	HQC Fan Filter Replacement Kit (5 filters/pk)
REKP	20 Amp AC Power Kit w/Receptacle, Box, Flexible Conduit
REKGB	Grounding Kit with Busbar and Jumpers
REKFP	Fiber Optic Bracket for one FSP or Cassette
HWK6M6	Rear Rail Kit with two rails, 24" x M6
HWK9M6	Rear Rail Kit with two rails, 36" x M6
HWK12M6	Rear Rail Kit with two rails, 48" x M6
HWK241224	Rear Rail Kit with two rails, 24" x #12-24
HWK361224	Rear Rail Kit with two rails, 36" x #12-24
HWK481224	Rear Rail Kit with two rails, 48" x #12-24