



## Specifications

- 18 gauge cold rolled steel base
- White powder coat finish
- High impact thermoplastic ABS trim ring

## Standards

- cULus 1863 listed
- UL VO flame rating on ABS trim ring

## FPTV Connection Enclosures

White

Description	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Catalog No.
2-gang in-wall enclosure	8.16" (207)	7.92" (201)	3.37" (86)	<b>NSAV62M</b>
Steel cover for NSAV62M	7.2" (183)	7.2" (183)	0.05" (1)	<b>NSAV6C</b>
4-gang in-wall enclosure	14.80" (376)	7.92" (201)	3.37" (86)	<b>NSAV124M</b>
Steel cover for NSAV124M	13.80" (351)	7.2" (183)	0.05" (1)	<b>NSAV12C</b>



## Specifications

- Surface finish: white powder coat
- Enclosure: 18 gauge cold rolled steel
- Mounting brackets: 18 gauge welded steel

## AV Ceiling Enclosures

White, includes enclosure, (2) 20A duplex receptacles and 2-gang back box

Description	Catalog No.
Standard	<b>AVCE1</b>

