



Specifications

- Load capacity: 100lb.
- (1) pair 19" rack-style rails tapped 12-24 holes per EIA-310-D
- Finish: powder coat black
- Front door lockable
- Reversible and locked door

HEQ QUADCAB® Wall Mount Cabinets

Includes: (1) section, (1) front door, (2) 19" mounting angles, CH751 lock

Mesh Door Style

| Rack Units | Max. Switch Depth Inches (mm) | Height Inches (mm) | Width Inches (mm) | Depth Inches (mm) | Mesh DoorStyle |
|------------|-------------------------------|--------------------|-------------------|-------------------|----------------|
| 5 | 12" (305) | 12" (305) | 22.6" (574) | 14" (356) | HEQ12 |
| 8 | 12" (305) | 18" (457) | 22.6" (574) | 14" (356) | HEQ18 |
| 12 | 12" (305) | 24" (610) | 22.6" (574) | 14" (356) | HEQ24 |



Solid Door Style

| Rack Units | Max. Switch Depth Inches (mm) | Height Inches (mm) | Width Inches (mm) | Depth Inches (mm) | Solid DoorStyle |
|------------|-------------------------------|--------------------|-------------------|-------------------|-----------------|
| 5 | 12" (305) | 12" (305) | 22.6" (574) | 14" (356) | HEQ12S |
| 8 | 12" (305) | 18" (457) | 22.6" (574) | 14" (356) | HEQ18S |
| 12 | 12" (305) | 24" (610) | 22.6" (574) | 14" (356) | HEQ24S |

