



Specifications

- Load capacity: 250lb.
- (2) pair 19" rack-style rails tapped 12-24 holes per EIA-310-D
- Finish: powder coat black
- Three independent sections
- Front and rear door lockable
- U-style rear knockouts accommodate terminated cables
- Installed bonding jumpers

HLQ QUADCAB® Wall Mount Cabinets

Includes: (1) rear section, (1) front door, (2) 19" mounting angles, (1) center section with (2) CH751 locks, (3) bonding jumpers

Window Door Style

Rack Units	Max. Switch Depth Inches (mm)	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Load Capacity (lb)	Window Door Style
12	22" (559)	24" (610)	22" (559)	24" (610)	150	HLQ24
19	22" (559)	36" (914)	22" (559)	24" (610)	250	HLQ36
25	22" (559)	48" (1219)	22" (559)	24" (610)	250	HLQ48
12	30" (762)	24" (610)	22" (559)	32" (813)	250	HLQ2432
19	30" (762)	36" (914)	22" (559)	32" (813)	250	HLQ3632
25	30" (762)	48" (1219)	22" (559)	32" (813)	250	HLQ4832



Mesh Door Style

Rack Units	Max. Switch Depth Inches (mm)	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Load Capacity (lb)	Mesh Door Style
12	22" (559)	24" (610)	22" (559)	24" (610)	150	HLQ24M
19	22" (559)	36" (914)	22" (559)	24" (610)	250	HLQ36M
25	22" (559)	48" (1219)	22" (559)	24" (610)	350	HLQ48M
12	30" (762)	24" (610)	22" (559)	32" (813)	250	HLQ2432M
19	30" (762)	36" (914)	22" (559)	32" (813)	250	HLQ3632M
25	30" (762)	48" (1219)	22" (559)	32" (813)	250	HLQ4832M



Fan Kits

Description	Catalog No.
Fan Kit	HLQFK
Filter Kit	HLQFF
HLQxx32 Caster Kit (5 wheels)	HLQ32CK
HLQxx32 Dust Resistance Kit	HLQ32DRK

