



Specifications

- 4,000 lbs. static load and 2,500 lbs. dynamic load capacity on robust welded frame construction
- Locking sidewalls
- Removable top panel with full width brush grommet front and rear
- Mesh door 77% open for airflow
- Field reversible doors and handle with lock
- Includes (2) vertical cable management organizers and (2) rear PDU brackets
- Casters, leveling feet, and M6 cage nuts included

HDC Data Center Cabinets

RU	Height mm (Inch)	Width mm (Inch)	Depth mm (Inch)	Color	Catalog No.
42	2006 (79)	600 (24)	1100 (44)	Black	HDC422444BK
42	2006 (79)	600 (24)	1100 (44)	White	HDC422444WH
42	2006 (79)	600 (24)	1200 (48)	Black	HDC422448BK
42	2006 (79)	600 (24)	1200 (48)	White	HDC422448WH
42	2006 (79)	800 (32)	1100 (44)	Black	HDC423244BK
42	2006 (79)	800 (32)	1100 (44)	White	HDC423244WH
42	2006 (79)	800 (32)	1200 (48)	Black	HDC423248BK
42	2006 (79)	800 (32)	1200 (48)	White	HDC423248WH
45	2143 (84)	600 (24)	1100 (44)	Black	HDC452444BK
45	2143 (84)	600 (24)	1100 (44)	White	HDC452444WH
45	2143 (84)	600 (24)	1200 (48)	Black	HDC452448BK
45	2143 (84)	600 (24)	1200 (48)	White	HDC452448WH
45	2143 (84)	800 (32)	1100 (44)	Black	HDC453244BK
45	2143 (84)	800 (32)	1100 (44)	White	HDC453244WH
45	2143 (84)	800 (32)	1200 (48)	Black	HDC453248BK
45	2143 (84)	800 (32)	1200 (48)	White	HDC453248WH
48	2273 (89)	600 (24)	1100 (44)	Black	HDC482444BK
48	2273 (89)	600 (24)	1100 (44)	White	HDC482444WH
48	2273 (89)	600 (24)	1200 (48)	Black	HDC482448BK
48	2273 (89)	600 (24)	1100 (44)	White	HDC482444WH
48	2273 (89)	600 (24)	1200 (48)	Black	HDC482448BK
48	2273 (89)	600 (24)	1200 (48)	White	HDC482448WH
48	2273 (89)	800 (32)	1200 (48)	Black	HDC483248BK
48	2273 (89)	800 (32)	1200 (48)	White	HDC483248WH