



Raised Floor Pedestal Clamps

Pedestal	Wire Range	Configuration	Hardware	Install Torque	Catalog No.
0.75"-1.5" square 0.75"-1.875" round	6 – 4/OAWG	Grid or parallel	Stainless Steel ½"	120in-lb conductor 180in-lb clamp	HGBGXP1828RF
1.0"-1.25" round	4 – 2/OAWG	Parallel	Silicon Bronze 9/16"	240in-lb	HGBGP1526G1
0.75"-1.0" round or square	8 – 2AWG	Parallel	Silicon Bronze 9/16"	240in-lb	HGBGRF4C3

Note: Torque values may differ based on the Grounding and Bonding Standard selected.
The Mesh Bonding Network shall have a support attached at a maximum of 3' (36") intervals.

Pipe Clamps

I.P.S. Pipe Dia. Inches	Height Inches	Width Inches	Conductor Range	U-Bolt Size Inches	Nut Size Inches	Catalog No.
1.0"	2 ⁷ / ₈ "	2 ⁵ / ₈ "	4AWG-2/OAWG	3/8"	9/16"	HGBGAR1526
1.5"	3½"	3"	4AWG-2/OAWG	3/8"	9/16"	HGBGAR1726
2.0"	4"	3¼"	4AWG-2/OAWG	3/8"	9/16"	HGBGAR1826
2.5"	4¼"	3¾"	4AWG-2/OAWG	3/8"	9/16"	HGBGAR1926
3.0"	5"	4¼"	4AWG-2/OAWG	3/8"	9/16"	HGBGAR2026
3.5"	5 ⁵ / ₈ "	4¾"	4AWG-2/OAWG	3/8"	9/16"	HGBGAR2126
4.0"	6¼"	5 ³ / ₈ "	4AWG-2/OAWG	3/8"	9/16"	HGBGAR2226
6.0"	8 ¹³ / ₁₆ "	8 ³ / ₈ "	2AWG-250kcmil	½"	¾"	HGBGAR8629

Note: All pipe clamps secure the grounding conductor to the pipe in a parallel or perpendicular manner.