

Braided Jumper						
Length Inches (mm)	Width Inches (mm)	Hole Size Inches	Hole Spacing Inches (mm)	Qty	Catalog No.	
6" (152)	0.5" (13)	¼"	-	10	HGBBD6S10	
9" (229)	0.5" (13)	¼"	-	10	HGBBD9S10	
8" (203)	0.94" (24)	⅜"	1.0" (25)	1	HGBBD8	
12" (305)	0.94" (24)	⅜"	1.25" (32)	1	HGBBD12	
18" (457)	0.94" (24)	⅜"	1.25" (32)	1	HGBBD18	
24" (610)	0.94" (24)	⅜"	1.25" (32)	1	HGBBD24	

QUADCAB® Wall Mount Cabinet Ground Kit		
Description		Catalog No.
Ground bar with (6) ¼"-20 male studs; (2) ¼"-20 carriage bolts and isolating hardware; (2) ground straps; (6) ¼"-20 nuts with star washers		REKGB



High Flex Jumper				
Color	Gauge	Length	Catalog No.	
Green/Yellow	#10 AWG	7"	HGBHF7	
		9"	HGBHF9	
		12"	HGBHF12	
		14"	HGBHF14	
		18"	HGBHF18	
		24"	HGBHF24	
		30"	HGBHF30	