




















**Installation Accessories**


Description	Qty	Catalog No.	
ESD port for 4mm banana plug; 0.5oz Penetrox™; ESD Label; (2) #12-24 TFS; (2) M6 stainless TFS	10	<b>HGBESDKT10</b>	
1/4" belleville washer	50	<b>HGB25CNWH</b>	
3/8" belleville washer	50	<b>HGB38CNWH</b>	
#12-24 x 3/4" stainless steel screws	50	<b>HGB1224ST</b>	
M6 x 16mm stainless steel screws	50	<b>HGBM6ST</b>	
ESD label	25	<b>HGBESDLBL</b>	
Ground label	25	<b>HGBGNLDBL</b>	
Ground wire label	25	<b>HGRKTLBL</b>	

Description	Qty	Catalog No.	
ESD cloth bracelet; 6ft cord; 4mm banana plug	1	<b>HGBESDBC</b>	
ESD metal bracelet; 6ft cord; 4mm banana plug	1	<b>HGBESDBM</b>	
3/16" drill bit for steel material and 1/4" thread forming screw	1	<b>HGB025DBS</b>	
Wire brush for power drill	1	<b>HGBCWB2</b>	
2" x 4" abrasive pad	6	<b>HGB24AP</b>	
8oz bottle Penetrox™	1	<b>HGBP8A</b>	
0.5oz tube Penetrox™	50	<b>HPENEA0550</b>	
Serrated paint piercing washer	50	<b>HGB25PPW</b>	


**Braided Jumper**

Length Inches (mm)	Width Inches (mm)	Hole Size Inches	Hole Spacing Inches (mm)	Qty	Catalog No.	
6" (152)	0.5" (13)	1/4"	-	10	<b>HGBBD6S10</b>	
9" (229)	0.5" (13)	1/4"	-	10	<b>HGBBD9S10</b>	
8" (203)	0.94" (24)	3/8"	1.0" (25)	1	<b>HGBBD8</b>	
12" (305)	0.94" (24)	3/8"	1.25" (32)	1	<b>HGBBD12</b>	
18" (457)	0.94" (24)	3/8"	1.25" (32)	1	<b>HGBBD18</b>	
24" (610)	0.94" (24)	3/8"	1.25" (32)	1	<b>HGBBD24</b>	

**QUADCAB® Wall Mount Cabinet Ground Kit**

Description	Catalog No.	
Ground bar with (6) 1/4"-20 male studs; (2) 1/4"-20 carriage bolts and isolating hardware; (2) ground straps; (6) 1/4"-20 nuts with star washers	<b>REKGB</b>	

**High Flex Jumper**

Color	Gauge	Length	Catalog No.	
Green/Yellow	#10 AWG	7"	<b>HGBHF7</b>	
		9"	<b>HGBHF9</b>	
		12"	<b>HGBHF12</b>	
		14"	<b>HGBHF14</b>	
		18"	<b>HGBHF18</b>	
		24"	<b>HGBHF24</b>	
		30"	<b>HGBHF30</b>	