



**Raised Floor Pedestal Clamps**

Pedestal	Wire Range	Configuration	Hardware	Install Torque	Catalog No.
0.75"-1.5" square 0.75"-1.875" round	6 - 4/0AWG	Grid or parallel	Stainless Steel 1/2"	120in-lb conductor 180in-lb clamp	<b>HGBGXP1828RF</b>
1.0"-1.25" round	4 - 2/0AWG	Parallel	Silicon Bronze 9/16"	240in-lb	<b>HGBGP1526G1</b>
0.75"-1.0" round or square	8 - 2AWG	Parallel	Silicon Bronze 9/16"	240in-lb	<b>HGBGRF4C3</b>



*Note: Torque values may differ based on the Grounding and Bonding Standard selected. The Mesh Bonding Network shall have a support attached at a maximum of 3' (36") intervals.*

**Pipe Clamps**

I.P.S. Pipe Dia. Inches	Height Inches	Width Inches	Conductor Range	U-Bolt Size Inches	Nut Size Inches	Catalog No.
1.0"	2 7/8"	2 5/8"	4AWG-2/0AWG	3/8"	9/16"	<b>HGBGAR1526</b>
1.5"	3 1/2"	3"	4AWG-2/0AWG	3/8"	9/16"	<b>HGBGAR1726</b>
2.0"	4"	3 1/4"	4AWG-2/0AWG	3/8"	9/16"	<b>HGBGAR1826</b>
2.5"	4 1/4"	3 3/4"	4AWG-2/0AWG	3/8"	9/16"	<b>HGBGAR1926</b>
3.0"	5"	4 1/4"	4AWG-2/0AWG	3/8"	9/16"	<b>HGBGAR2026</b>
3.5"	5 5/8"	4 3/4"	4AWG-2/0AWG	3/8"	9/16"	<b>HGBGAR2126</b>
4.0"	6 1/4"	5 3/8"	4AWG-2/0AWG	3/8"	9/16"	<b>HGBGAR2226</b>
6.0"	8 13/16"	8 3/8"	2AWG-250kcmil	1/2"	3/4"	<b>HGBGAR8629</b>



*Note: All pipe clamps secure the grounding conductor to the pipe in a parallel or perpendicular manner.*