

Braided Jumper

Length Inches (mm)	Width Inches (mm)	Hole Size Inches	Hole Spacing Inches (mm)	Qty	Catalog No.
6" (152)	0.5" (13)	¼"	-	10	HGBBD6S10
9" (229)	0.5" (13)	¼"	-	10	HGBBD9S10
8" (203)	0.94" (24)	⅜"	1.0" (25)	1	HGBBD8
12" (305)	0.94" (24)	⅜"	1.25" (32)	1	HGBBD12
18" (457)	0.94" (24)	⅜"	1.25" (32)	1	HGBBD18
24" (610)	0.94" (24)	⅜"	1.25" (32)	1	HGBBD24



QUADCAB® Wall Mount Cabinet Ground Kit

Description	Catalog No.
Ground bar with (6) ¼"-20 male studs; (2) ¼"-20 carriage bolts and isolating hardware; (2) ground straps; (6) ¼"-20 nuts with star washers	REKGB



High Flex Jumper

Color	Gauge	Length	Catalog No.
Green/Yellow	#10 AWG	7"	HGBHF7
		9"	HGBHF9
		12"	HGBHF12
		14"	HGBHF14
		18"	HGBHF18
		24"	HGBHF24
		30"	HGBHF30

