



HDMI Active Optical Cables

Features

- 4K High Speed HDMI Transmission
- Small diameter flexible cable helps with installation
- Plenum rated, installs in any environment
- Micro-USB connection and optional 5VDC adapter kit boost power
- Source and display connector labels identify proper installation direction

4K @ 60 Hz Active Optical HDMI Cables

- 18 Gbps High Speed
- Maximum resolution: 4K (4096 × 2160 or 3840 × 2160) at 30 or 60Hz; 4:4:4 chroma
- HDCP 2.2; EDID; CEC; FCC
- Diameter: 5.2 ± 0.2 mm
- Plenum rated
- Bending radius: 0.8 in. (20 mm)
- Operating temperature: 32-131° F (0-55° C)
- Gold Plated HDMI Type A Male Connectors

HDMI Patch Cables

- HDMI 4K@ 60 Hz
- 18 Gbps High Speed with Ethernet
- Thin 6mm±0.2, High Flex

4K @ 60 Hz Active Optical HDMI Cables	
Description	Catalog No.
HDMI, AOC, Black, 20 ft.	HCHX20BK
HDMI, AOC, Black, 30 ft.	HCHX30BK
HDMI, AOC, Black, 60 ft.	HCHX60BK
HDMI, AOC, Black, 100 ft.	HCHX100BK

5V DC Power Adapter Kit	
Description	Catalog No.
5V DC Power Kit for Active Optical Cords	HDMDC5V2

HDMI 4K Connectors for IMB and ISFB Series Blanks			
Color	HDMI Keystone Feed-Thru	HDMI Feed-Thru Coupler	HDMI Feed-Thru 3-Inch Tail
Black	SFHC14BK	HDMIC14	HDMIT14
White	SFHC14W	-	-

HDMI Device Patch Cords	
24AWG	
Length (ft)	Catalog No.
3'	HCH03BK
6'	HCH06BK
10'	HCH10BK

Note: Black and non-plenum only.

HDMI 4K Decorator Frames		
Color	1-Port	2-Port
Black	NS801BK	NS802BK
Ivory	NS801I	NS802I
Gray	NS801GY	NS802GY
Light Almond	NS801LA	NS802LA
White	NS801W	NS802W