



Dimensions Inches (mm)

Style	Rectangular Cover		Round Cover	
Box Type				
Standard	CFB45G55E	-	CFB45G55RE	-
Box Corrosion-Resistant Box (On-grade)	-	CFB45G55CRE	-	CFB45G55RCRE
Recommended Pour Depth	6.00" (152.4)	6.00" (152.4)	6.25" (158.8)	6.25" (158.8)
Min. Depth of Pour	5.50" (139.7)	5.50" (139.7)	6.25" (158.8)	6.25" (158.8)
Adjustability	Fully	Fully	Fully	Fully
Cubic Inch (cm³) Capacity per Gang	99/105 cu. in.	99/105 cu. in.	99/105 cu. in.	99/105 cu. in.
	(1621/1721 cm ³)	(1621/1721 cm ³)	(1621/1721 cm ³)	(1621/1721 cm ³)
Dimensions - A	5.59" (142.0)	5.59" (142.0)	-	-
Dimensions - B	11.09" (281.6)	11.09" (281.6)	11.09" (281.6)	11.09" (281.6)
Dimensions - C	14.14" (359.2)	14.14" (359.2)	14.14" (359.2)	14.14" (359.2)
Dimensions - D	-	-	8.37" (212.5) TYP.	8.37" (212.5) TYP.
Dimensions - E	5.50" (139.7)	5.50" (139.7)	6.25" (158.8)	6.25" (158.8)
KO Trade Size: Ends	(2) 3/4", 1", 1 1/4", 2"*	(2) 3/4", 1", 1 1/4", 2"*	(2) 3/4", 1", 1 1/4", 2"*	(2) 3/4", 1", 1 1/4", 2"*
Sides	(2) 3/4", 1", 1 1/4", 2"*	(2) 3/4", 1", 1 1/4", 2"*	(2) 3/4", 1", 1 1/4", 2"*	(2) 3/4", 1", 1 1/4", 2"*
Bottom	(2) 1/2", 3/4", 1", 1 1/4"	(2) 1/2", 3/4", 1", 1 1/4"	(2) 1/2", 3/4", 1", 1 1/4"	(2) 1/2", 3/4", 1", 1 1/4"
Cover Style	Rectangular	Rectangular	Round	Round
2 Inch Hub Compatible	Yes	Yes	Yes	Yes

Note: UL File Number E31999. Boxes include concrete covers.

*Requires CFBHUB2 for 2" conduits. CFBHUB200PVC for 2" PVC conduits or CFBHUB125PVC for 1 1/4" PVC conduits.

Rectangular Covers

- Compatible with CFB45G55E and CFB45G55CRE Series Floor Boxes
- Two large cable egress doors and access 180° opening
- Maximum static load of 1500lb with 2x safety factor**
- Surface style typical applications: carpet, VCT
- Flush style typical applications: tile, finished concrete and terrazzo floors

Finish	Surface Cover Flange Dimensions 11 1/2" x 10"		Flush Cover Flange Dimensions 10 1/2" x 9"	
	Without Insert	With Insert	Without Insert	With Insert
Aluminum Powder Coat	610GCCVRALU	610GCCVRALUC	610GTCVRALU	610GTCVRALUC
Black Powder Coat	610GCCVRBK	610GCCVRBK C	610GTCVRBK	610GTCVRBK C
Brass Powder Coat	610GCCVRBRS	610GCCVRBRSC	610GTCVRBRS	610GTCVRBRSC
Bronze Powder Coat	610GCCVRBRZ	610GCCVRBRZC	610GTCVRBRZ	610GTCVRBRZC
Satin Nickel Powder Coat	610GCCVRNK	610GCCVRNK C	610GTCVRNK	610GTCVRNK C



Round Covers

- Compatible with CFB45G55RE and CFB45G55RCRE Series Floor Boxes
- Cover flanges have a 9 1/2 in. diameter and 0.15 in. height
- Maximum static load of 1,000 lbs. with 2x safety factor**
- Recessed covers- 180° access with 2 cable egress doors

Finish	Surface
Brushed Aluminum	CFBS1R8CVRALU
Black Powder Coated	CFBS1R8CVRBLK
Brass Plated	CFBS1R8CVRBRS
Bronze Plated	CFBS1R8CVRBRZ
Gray Powder Coat	CFBS1R8CVRGRY
Satin Nickel Plated	CFBS1R8CVRNKL



**Load applied through a 3" (76mm) mandrel in center of the cover

ScrubShield

Complies with UL514 A