



1



2

3



4



5



6

Three Service Aluminum Service Poles

Description	Color		10' 2" (3.10m)	12' 2" (3.71m)	15' 2" (4.62m)
(2) 20A 125V Style Line® duplex receptacles; one circuit	Black	□	HBLPP10BK	HBLPP12BK	HBLPP15BK
	Gray	□	HBLPP10A	HBLPP12A	HBLPP15A
	Ivory	□	HBLPP10AI	HBLPP12AI	HBLPP15AI
	Office White	①	HBLPP10OW	HBLPP12OW	HBLPP15OW
	White		HBLPP10W	HBLPP12W	HBLPP15W
	Clear Anod. Aluminum		HBLPP10AAL	HBLPP12AAL	HBLPP15AAL
(1) Orange isolated ground 20A 125V Style Line duplex receptacle; (1) 20A 125V Style Line duplex receptacle; two circuits	Black	□	HBLPP10IGBK	-	-
	Gray	□	HBLPP10IGA	-	-
	Ivory	□	HBLPP10IGAI	-	-
	Office White	②	HBLPP10IGOW	-	-
	White		HBLPP10IGW	-	-
	Clear Anod. Aluminum		HBLPP10IGAL	-	-
(2) Orange isolated ground 20A 125V Style Line duplex receptacles; (1) isolated ground surge suppression 20A 125V duplex receptacle; one circuit	Black	□	HBLPP10SBK	-	-
	Gray	□	HBLPP10SA	-	-
	Ivory	□	HBLPP10SAI	-	-
	Office White	③	HBLPP10SOW	-	-
	White		HBLPP10SW	-	-
	Clear Anod. Aluminum		HBLPP10SAL	-	-
(1) 20A 125V GFCI Self Test duplex receptacle with (2) ground fault protected 20A 125V Style Line duplex receptacles; one circuit	Black	□	HBLPP10GFBK	HBLPP12GFBK	HBLPP15GFBK
	Gray	□	HBLPP10GF	HBLPP12GF	HBLPP15GF
	Ivory	□	HBLPP10GFI	HBLPP12GFI	HBLPP15GFI
	Office White	□	HBLPP10GFOW	HBLPP12GFOW	HBLPP15GFOW
	White	□	HBLPP10GFW	HBLPP12GFW	HBLPP15GFW
	Clear Anod. Aluminum	④	HBLPP10GFAL	HBLPP12GFAL	HBLPP15GFAL
Blank pole; divider; (4) Style Line device knockouts	Black		HBLPPOBK	HBLPPO12BK	HBLPPO15BK
	Gray		HBLPPOA	HBLPPO12A	HBLPPO15A
	Ivory		HBLPPOAI	HBLPPO12AI	HBLPPO15AI
	Office White		HBLPPOOW	HBLPPO12OW	HBLPPO15OW
	White		HBLPPOW	HBLPPO12W	HBLPPO15W
	Clear Anod. Aluminum		HBLPPOAAL	HBLPPO12AAL	HBLPPO15AAL

Accessories

Description	Catalog No.
Adjustable T-bar assembly for mounting poles in the middle of ceiling tile	⑤ ATB*
Replacement service pole trim kit (Office White)	⑥ PPTRIM1*

*Note: UL Listed

Dimensions

Inches (mm)

