



## Dimensions Inches (mm)

| Style  | Rectangular Cover                     |                                       | Round Cover                           |                                       |
|--|---------------------------------------|---------------------------------------|---------------------------------------|---------------------------------------|
|  |                                       |                                       |                                       |                                       |
| <b>Box Type</b>                                      |                                       |                                       |                                       |                                       |
| <b>Standard Box</b>                                  | <b>CFB4G30E</b>                       | <b>CFB4G25E</b>                       | <b>CFB4G30RE</b>                      | <b>CFB4G25RE</b>                      |
| <b>Corrosion-Resistant (On-grade)</b>                | <b>CFB4G30CRE</b>                     | <b>CFB4G25CRE</b>                     | <b>CFB4G30RCRE</b>                    | <b>CFB4G25RCRE</b>                    |
| <b>Recommended Pour Depth</b>                        | 3.50" (88.9)                          | 3.00" (76.2)                          | 3.75" (95.3)                          | 3.25" (82.6)                          |
| <b>Min. Depth of Pour</b>                            | 3.00" (76.2)                          | 2.50" (63.5)                          | 3.75" (95.3)                          | 3.25" (82.6)                          |
| <b>Adjustability</b>                                 | Fully                                 | Fully                                 | Fully                                 | Fully                                 |
| <b>Cubic Inch (cm<sup>3</sup>) Capacity per Gang</b> | 51.0 cu. in. (835.0 cm <sup>3</sup> ) | 41.5 cu. in. (680.0 cm <sup>3</sup> ) | 51.0 cu. in. (835.0 cm <sup>3</sup> ) | 41.5 cu. in. (680.0 cm <sup>3</sup> ) |
| <b>Dimensions - A</b>                                | 3.00" (76.2)                          | 2.50" (63.5)                          | -                                     | -                                     |
| <b>Dimensions - B</b>                                | 11.33" (276.5)                        | 11.20" (284.5)                        | 11.20" (284.5)                        | 11.20" (284.5)                        |
| <b>Dimensions - C</b>                                | 14.57" (370.1)                        | 14.57" (370.1)                        | 14.57" (370.1)                        | 14.57" (370.1)                        |
| <b>Dimensions - D</b>                                | -                                     | -                                     | 8.37" (212.5) TYP.                    | 8.37" (212.5) TYP.                    |
| <b>Dimensions - E</b>                                | 3.50" (88.9)                          | 3.00" (76.2)                          | 3.75" (95.3)                          | 3.25" (82.6)                          |
| <b>KO Trade Size: Ends</b>                           | (4) 1/2", 3/4", 1", 1 1/4"            | (4) 1/2", 3/4", 1"                    | (4) 1/2", 3/4", 1", 1 1/4"            | (4) 1/2", 3/4", 1"                    |
| <b>Sides</b>   | (4) 3/4", 1", 1 1/4", 2"*             | (4) 1/2", 3/4", 1"                    | (4) 3/4", 1", 1 1/4", 2"*             | (4) 1/2", 3/4", 1"                    |
| <b>Bottom</b>  | (4) 1/2", 3/4", 1", 1 1/4"            | (4) 1/2", 3/4", (4) 1", 1 1/4"        | (4) 1/2", 3/4", 1", 1 1/4"            | (4) 1/2", 3/4", (4) 1", 1 1/4"        |
| <b>Cover Style</b>                                   | Rectangular                           | Rectangular                           | Round                                 | Round                                 |
| <b>2 Inch Hub Compatible</b>                         | Yes                                   | No                                    | Yes                                   | No                                    |

Note: UL File Number E31999. Boxes include concrete covers.  
 \*Requires CFBHUB2 for 2" conduits. CFBHUB200PVC for 2" PVC conduits or CFBHUB125PVC for 1 1/4" PVC conduits.

### Rectangular Covers

- Compatible with CFB4G25, CFB4G25CR, CFB4G30 and CFB4G30CR Series Floor Boxes
- Two large cable egress doors and access 180° opening
- Maximum static load of 800 lbs. with 2x safety factor\*
- Surface style typical applications: Carpet, VCT
- Flush style typical applications: Tile, finished concrete and Terrazzo floors
- Furniture Feed covers ship with low voltage dividers

| Finish                   | Surface Cover Flange Dimensions 11n" x 7x" |             |                                  | Flush Cover Flange Dimensions 10n" x 6x" |             |                                  |
|--------------------------|--|-------------|----------------------------------|--|-------------|----------------------------------|
|                          | Without Insert                             | With Insert | Furniture Feed (1" and 2" Plugs) | Without Insert                           | With Insert | Furniture Feed (1" and 2" Plugs) |
| Aluminum Powder Coat     | 24GCCVRALU                                 | 24GCCVRALUC | 24GCFFCVRALU                     | 24GTCVRALU                               | 24GTCVRALUC | 24GTTFCVRALU                     |
| Black Powder Coat        | 24GCCVRBK                                  | 24GCCVRBK   | 24GCFFCVRBK                      | 24GTCVRBK                                | 24GTCVRBK   | 24GTTFCVRBK                      |
| Brass Powder Coat        | 24GCCVRBRS                                 | 24GCCVRBRS  | 24GCFFCVRBRS                     | 24GTCVRBRS                               | 24GTCVRBRS  | 24GTTFCVRBRS                     |
| Bronze Powder Coat       | 24GCCVRBRZ                                 | 24GCCVRBRZ  | 24GCFFCVRBRZ                     | 24GTCVRBRZ                               | 24GTCVRBRZ  | 24GTTFCVRBRZ                     |
| Satin Nickel Powder Coat | 24GCCVRNK                                  | 24GCCVRNK   | 24GCFFCVRNK                      | 24GTCVRNK                                | 24GTCVRNK   | 24GTTFCVRNK                      |

### Round Covers

- Compatible with CFB4G25R, CFB4G25RCR, CFB4G30R, and CFB4G30RCR Series Floor Boxes
- Cover flanges have a 9 1/2 in. diameter and 0.15 in. height
- Maximum static load of 1,000 lbs. with 2x safety factor\*
- Recessed covers- 180° access with 2 cable egress doors
- Furniture Feed covers dividers purchased separately

| Finish              | Flush Surface | Furniture Feed (1 in. and 2 in. Plugs) |
|---------------------|---------------|--|
| Brushed Aluminum    | CFBS1R8CVRALU | CFBS1R8FFCVRALU**                      |
| Black Powder Coat   | CFBS1R8CVRBLK | CFBS1R8FFCVRBLK**                      |
| Brass Plated        | CFBS1R8CVRBRS | CFBS1R8FFCVRBRS**                      |
| Bronze Plated       | CFBS1R8CVRBRZ | CFBS1R8FFCVRBRZ**                      |
| Gray Powder Coat    | CFBS1R8CVRGRY | CFBS1R8FFCVRGRY**                      |
| Satin Nickel Plated | CFBS1R8CVRNKL | CFBS1R8FFCVRNKL**                      |



\*Load applied through a 3" (76mm) mandrel in center of the cover.  
 \*\* For 4-gang box dual service, **CFBS1R8FF4GDIVKIT** required with Furniture Feed covers. Purchased separately.

**ScrubShield**  
Complies with UL514 A

Delivery - Section T